


**ZQV 4N/8**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), Plugged, orange, 32 A, Number of poles: 8, Pitch in mm (P): 6.10, Insulated: Yes, Width: 46.5 mm
Order No.	<a href="#">1528030000</a>
Type	ZQV 4N/8
GTIN (EAN)	4050118332841
Qty.	20 items

## ZQV 4N/8

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



RoHS

Conform

## Dimensions and weights

Depth	27.95 mm
Height	2.8 mm
Width	46.5 mm
Net weight	5.75 g

Depth (inches)	1.1004 inch
Height (inches)	0.1102 inch
Width (inches)	1.8307 inch

## Temperatures

Storage temperature	-25 °C...55 °C
Operating temperature	-60 °C...130 °C
Continuous operating temp., max.	130 °C

Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

## Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes
----------------	---------	--------------------------	-----

## Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

## General

Number of poles	8
-----------------	---

## Rating data

Rated voltage	400 V	Nominal current	32 A
---------------	-------	-----------------	------

## Important note

Product information	Due to stability and temperature reasons it is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400V. The voltage is reduced to 25V if cut cross connection with blank cut edges are used.
---------------------	--

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03

**ZQV 4N/8**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

**Technical data**

[www.weidmueller.com](http://www.weidmueller.com)

---

ECLASS 15.0

27-25-03-03

---