


**ZQV 4N/5 BL****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |                                                                                                                            |
|------------|----------------------------------------------------------------------------------------------------------------------------|
| Version    | Cross-connector (terminal), Plugged, blue, 32 A, Number of poles: 5, Pitch in mm (P): 6.10, Insulated: Yes, Width: 28.2 mm |
| Order No.  | <a href="#">1528140000</a>                                                                                                 |
| Type       | ZQV 4N/5 BL                                                                                                                |
| GTIN (EAN) | 4050118333015                                                                                                              |
| Qty.       | 60 items                                                                                                                   |

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 27.95 mm | Depth (inches)  | 1.1004 inch |
| Height     | 2.8 mm   | Height (inches) | 0.1102 inch |
| Width      | 28.2 mm  | Width (inches)  | 1.1102 inch |
| Net weight | 1.43 g   |                 |             |

### Temperatures

|                                  |                 |                                  |               |
|----------------------------------|-----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C  | Ambient temperature              | -5 °C...40 °C |
| Operating temperature            | -60 °C...130 °C | Continuous operating temp., min. | -60 °C        |
| Continuous operating temp., max. | 130 °C          |                                  |               |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Basic material            | Wemid | Colour | blue |
| UL 94 flammability rating | V-0   |        |      |

### Additional technical data

|                |         |                          |     |
|----------------|---------|--------------------------|-----|
| Type of fixing | Plugged | Explosion-tested version | Yes |
|----------------|---------|--------------------------|-----|

### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 6.10 mm |
|-----------------|---------|

### General

|                 |   |
|-----------------|---|
| Number of poles | 5 |
|-----------------|---|

### Rating data

|               |       |                 |      |
|---------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 32 A |
|---------------|-------|-----------------|------|

### Important note

|                     |                                                                                                                                                                                                                                                         |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used. |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Classifications

|           |          |             |             |
|-----------|----------|-------------|-------------|
| ETIM 8.0  | EC000489 | ETIM 9.0    | EC000489    |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |

## Technical data

ECLASS 15.0

27-25-03-03