

KLIPPON CS POK 122209-2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



On-site control with Ex-certified Klippon® Control Station: small command and signalling devices.

Approved operating and display elements in stainless steel, aluminium or polyester enclosures.

You want to control and safeguard your work processes in hazardous areas. For on-site control - approved Klippon® enclosure solutions with control and display elements.

General ordering data

Version	Klippon Control Station (control and signalling device), Control / signalling device, KLIPPON POK 122209 EX Glass-fibre reinforced polyester with graphite mixture, Pushbutton - green, Pushbutton - red, Pushbutton - green, 3 NC contact, 3 NO contacts, -55 °C...55 °C, IP54, IP66
Order No.	153715000
Type	KLIPPON CS POK 122209-2
GTIN (EAN)	4050118341218
Qty.	1 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00

Creation date 03.03.2026 07:25:43 MEZ

Catalogue status / Drawings

KLIPPON CS POK 122209-2

Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



 ROHS Conform

Dimensions and weights

Depth	90 mm	Depth (inches)	3.5433 inch
Depth with add-on components	103 mm	Height	220 mm
Height (inches)	8.6614 inch	Height of lowest version	90 mm
Width	120 mm	Width (inches)	4.7244 inch
Mounting dimension - height	82 mm	Mounting dimension - width	204 mm
Net weight	1686 g		

Temperatures

 Ambient temperature -55 °C...55 °C Operating temperature -55 °C...55 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	afb385d0-c52b-4449-8502-203596817ab0

Certificate numbers enclosure

Certificate no. Terminal Box (ATEX)	TÜV 14 ATEX 7606 X	Certificate no. Terminal Box (INMETRO)	LMP 21.0019X
Certificate no. Terminal Box (IECEX)	IECEX ITA 14.0013X	Certificate No. (IECEX)	IECEXITA14.0013X
Certificate No. (ATEX)	TUEV14ATEX7606X		

General information

1 Position in enclosure	Pushbutton - green	2 Position in enclosure	Pushbutton - red
3 Position in enclosure	Pushbutton - green	Contact design	3 NC contact, 3 NO contacts
Operating voltage, max.	400 V	Operating current at 40°C ambient temperature, max.	1.5 mm ² - T6 10 A, 1.5 mm ² - T5 16 A, 2.5 mm ² - T6 16 A
Operating current at 55°C ambient temperature, max.	1.5 mm ² - T4 16 A, 1.5 mm ² - T5 10 A, 2.5 mm ² - T5 16 A	Actuators	Pushbutton
Actuator colour	green, red	Drill holes side B	1 x M25
UL 94 flammability rating	V-0	Lid attachment	Crosshead screws, stainless steel
Seal material of operating and display elements	EPDM	Enclosure seal material	Silicone (VMQ)
Torque for lid screws	2.5 Nm	External earth	Available on request
Cable gland	VG M25 EXE 12-17 CR7J G4	Marking	II 2 G Ex d e IIC T* Gb, II 2 D Ex tb IIIC T*°C Db
Cable gland clamping area, max.	17 mm	Cable gland clamping area, min.	12 mm
Wire connection cross section, finely stranded, max.	2.5 mm ²	Type of mounting	Wall mounting
Surface finish	untreated	Reference product	KLIPPON POK 122209 EX

KLIPPON CS POK 122209-2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Impact resistance	7 joules in acc. with IEC60079-0	Temperature class	T4, T5, T6
Basic material	Glass-fibre reinforced polyester with graphite mixture		

Material data

UL 94 flammability rating	V-0	Surface finish	untreated
Basic material	Glass-fibre reinforced polyester with graphite mixture		

General data

Colour	graphite black	Protection degree	IP54, IP66
Colour chart (similar)	RAL 9011		

Housing

Basic material	Glass-fibre reinforced polyester with graphite mixture	Drill holes side B	1 x M25
----------------	--	--------------------	---------

Standard features

Version	Ex-approved housing solutions with control and display elements	Reference product	KLIPPON POK 122209 EX
---------	---	-------------------	---------------------------------------

Classifications

ETIM 8.0	EC002503	ETIM 9.0	EC002503
ETIM 10.0	EC002503	ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		

KLIPPON CS POK 122209-2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

