

## SAI-WDF 8P M12 M16

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Panel feed-through, Number of poles: 8, Coding: A-coded, M12, 30 V
Order No.	<a href="#">1543490000</a>
Type	SAI-WDF 8P M12 M16
GTIN (EAN)	4050118348170
Qty.	1 items

**SAI-WDF 8P M12 M16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E307231

**Dimensions and weights**

Net weight	24 g
------------	------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

**Technical data customisable plug-in connectors**

Number of poles	8	Coding	A-coded
Contact surface	Au (Gold)	Nominal voltage	30 V
Nominal current	1.5 A	Protection degree	IP67
Pollution severity	3	Rated current	Contacts 1-4 8A, contact 5 2A, 2 A (8-pole)
Shield connection	Yes	Threaded ring material	Diecast zinc
Temperature range of housing	-25...+85 °C		

**General technical specifications**

Number of poles	8	Coding	A-coded
Connection thread	M12	Contact surface	Au (Gold)
Nominal voltage	30 V	Nominal current	1.5 A
Protection degree	IP67	Pollution severity	3
Threaded ring material	Diecast zinc	Temperature range of housing	-25...+85 °C

**Classifications**

ETIM 8.0	EC002925	ETIM 9.0	EC002925
ETIM 10.0	EC002925	ECLASS 14.0	27-44-01-06
ECLASS 15.0	27-44-01-06		


SAI-WDF 8P M12 M16

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


www.weidmueller.com

Drawings

Drawing



Pole scheme



Pole scheme

