BLZ/SL KO BK BX



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery. Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

General ordering data

PCB plug-in connector, Accessories, Coding element, black, Number of poles: 1	
<u>1545710000</u>	
BLZ/SL KO BK BX	
4008190087142	
50 items	
Вох	



BLZ/SL KO BK BX



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

ROHS	Conform			
Dimensions and weights				
Net weight	0.8 g			
Environmental Product Comp	liance			
RoHS Compliance Status	Compliant without exemption			
REACH SVHC	No SVHC above 0.1 wt%			
Material data				
Insulating material	PBT GF	Colour	black	
Colour chart (similar)	RAL 9011	Moisture Level (MSL)		
UL 94 flammability rating	V-0	Storage temperature, min.	-40 °C	
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C	
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C	
Temperature range, installation, max.	100 °C			
Rated data acc. to IEC				
tested acc. to standard	IEC 60664-1, IEC 61984			
Packing				
Packaging	Box	VPE length	90.00 mm	
VPE width	70.00 mm	VPE height	42.00 mm	
Important note				
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the product can be evaluated on request.			
			urther claims on the product	
Notes	can be evaluated on rec		·	
Notes Classifications	can be evaluated on recLong term storage of	quest.	·	
Classifications	• Long term storage of 70%, 36 months	quest. the product with average temperature of 50°	C and maximum humidity	
Classifications ETIM 6.0	• Long term storage of 70%, 36 months EC002943	quest. the product with average temperature of 50° ETIM 7.0	C and maximum humidity EC002943	
Classifications ETIM 6.0 ETIM 8.0	can be evaluated on rec • Long term storage of 70%, 36 months EC002943 EC002943	quest. The product with average temperature of 50 ° ETIM 7.0 ETIM 9.0	EC002943	
Classifications ETIM 6.0 ETIM 8.0 ETIM 10.0	can be evaluated on rec • Long term storage of 70%, 36 months EC002943 EC002943 EC002943	rquest. The product with average temperature of 50 ° ETIM 7.0 ETIM 9.0 ECLASS 9.0	EC002943 EC002943 27-44-04-92	
Classifications ETIM 6.0 ETIM 8.0 ETIM 10.0 ECLASS 9.1	ecan be evaluated on recovery the control of the co	the product with average temperature of 50 ° ETIM 7.0 ETIM 9.0 ECLASS 9.0 ECLASS 10.0	EC002943 EC002943 27-44-04-92 27-44-04-92	
Classifications ETIM 6.0 ETIM 8.0 ETIM 10.0	can be evaluated on rec • Long term storage of 70%, 36 months EC002943 EC002943 EC002943	rquest. The product with average temperature of 50 ° ETIM 7.0 ETIM 9.0 ECLASS 9.0	EC002943 EC002943 27-44-04-92	

Creation date 28.11.2025 10:14:40 MEZ

Catalogue status / Drawings 2