

## UR20-FBC-EIP-V2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Ethernet/IP



More performance. Simplified.

u-remote. Weidmüller u-remote – our innovative remote I/O concept with IP 20 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, and no more downtime for considerably improved performance and greater productivity.

Reduce the size of your cabinets with u-remote, thanks to the narrowest modular design on the market and the need for fewer power-feed modules. Our u-remote technology offers tool-free assembly while the modular “sandwich” design and integrated web server speed up installation, both in the cabinet and machine. Status LEDs on the channel and each u-remote module enable reliable diagnosis and rapid service.

Our products boost the availability of your machines and systems, and ensure smooth processes, from planning to operation.

u-remote stands for “More Performance.” Simplified.

## General ordering data

|            |  |
|------------|--|
| Version    | Remote I/O fieldbus coupler, IP20, Ethernet, EtherNet/IP |
| Order No.  | <a href="#">1550550000</a>                               |
| Type       | UR20-FBC-EIP-V2  |
| GTIN (EAN) | 4050118356885  |
| Qty.       | 1 items  |

## UR20-FBC-EIP-V2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E141197                    |

### Dimensions and weights

|                             |        |                 |             |
|-----------------------------|--------|-----------------|-------------|
| Depth                       | 76 mm  | Depth (inches)  | 2.9921 inch |
| Height                      | 120 mm | Height (inches) | 4.7244 inch |
| Width                       | 52 mm  | Width (inches)  | 2.0472 inch |
| Mounting dimension - height | 120 mm | Net weight      | 223 g       |

### Temperatures

|                     |                   |                       |                |
|---------------------|-------------------|-----------------------|----------------|
| Storage temperature | -40 °C ... +85 °C | Operating temperature | -20 °C...60 °C |
|---------------------|-------------------|-----------------------|----------------|

### Environmental Product Compliance

|                                      |   |
|--------------------------------------|---|
| RoHS Compliance Status               | Compliant with exemption  |
| RoHS Exemption (if applicable/known) | 7a, 7cl   |
| REACH SVHC                           | Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1 |
| SCIP                                 | 98e19a7e-033b-4e68-93e3-c47b30de875e                                  |

### Connection data

|  |                      |  |                     |
|--|----------------------|--|---------------------|
| Wire cross-section, finely stranded, max. (AWG)      | AWG 16               | Wire cross-section, finely stranded, min. (AWG)      | AWG 26              |
| Wire cross-section, solid, max. (AWG)                | AWG 16               | Wire cross-section, solid, min. (AWG)                | AWG 26              |
| Type of connection                                   | PUSH IN              | Wire cross-section, solid, max.                      | 1.5 mm <sup>2</sup> |
| Wire cross-section, solid, min.                      | 0.14 mm <sup>2</sup> | Wire connection cross section, finely stranded, max. | 1.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, min. | 0.14 mm <sup>2</sup> |  |                     |

### General data

|                          |  |                           |  |
|--------------------------|--|---------------------------|--|
| Vibration resistance     | 5 Hz ≤ f ≤ 8.4 Hz: 3.5-mm amplitude as per IEC 60068-2-6, 8.4 Hz ≤ f ≤ 150 Hz: 1 g acceleration as per IEC 60068-2-6 | UL 94 flammability rating | V-0  |
| Test voltage             | 500 V  | Surge voltage category    | II   |
| Pollution severity       | 2  | Mounting rail             | TS 35  |
| Air pressure (operation) | ≥ 795 hPa (height ≤ 2000 m) as per DIN EN 61131-2  | Air humidity (transport)  | 10% to 95%, non-condensing as per DIN EN 61131-2 |

## UR20-FBC-EIP-V2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

|                          |  |                        |  |
|--------------------------|--|------------------------|--|
| Air pressure (transport) | 1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2 | Air pressure (storage) | 1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2 |
| Air humidity (operation) | 10% to 95%, non-condensing as per DIN EN 61131-2                       | Air humidity (storage) | 10% to 95%, non-condensing as per DIN EN 61131-2                       |
| Shock                    | 15 g over 11 ms, half sinus wave, acc. to IEC 60068-2-27               |                        |  |

### Power supply

|   |  |  |                      |
|---|--|--|----------------------|
| Supply voltage  | 24 V DC +20 %/ -15 %, via the system bus | Feed current for the system, max.                | 4 A                  |
| Feed current for IIN (input current path), max.               | 10 A                                     | Current consumption from I <sub>sys</sub> , typ. | 100 mA               |
| Supply voltage for outputs                                    | 24 V DC +20 %/ -15 %                     | Supply voltage system and inputs                 | 24 V DC +20 %/ -15 % |
| Feed current for IOU <sub>T</sub> (output current path), max. | 10 A                                     |  |                      |

### System data

|                                      |                                    |  |                     |
|--------------------------------------|------------------------------------|--|---------------------|
| Module type                          | Bus coupler                        | Interface                              | u-remote system bus |
| Galvanic isolation                   | 500 V DC between the current paths | Process data                           | 988 Byte            |
| max. number of modules               | 64                                 | Configuration interface                | Micro USB 2.0       |
| Connection type                      | 2x RJ45 plug-in connectors         | Field bus protocol                     | EtherNet/IP         |
| Transmission rate of field bus, max. | 100 Mbit/s                         | Transmission speed of system bus, max. | 48 Mbit/s           |
| Parameter data                       | 4 kByte                            | Diagnostic data                        | 3008 Byte           |

### Important note

Product information      The matching end brackets are included with the coupler.

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001603    | ETIM 9.0    | EC001603    |
| ETIM 10.0   | EC001603    | ECLASS 14.0 | 27-24-26-07 |
| ECLASS 15.0 | 27-24-26-07 |             |             |


UR20-FBC-EIP-V2

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

Drawings

Block diagram




Connection diagram



Explanation of abbreviations

Field bus coupler



## UR20-FBC-EIP-V2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Accessories



#### System accessory

Discover a wide range of accessories for your u-remote system - the ideal addition to make your applications even more efficient and flexible.

### General ordering data

|            |                            |                |  |
|------------|----------------------------|----------------|--|
| Type       | UR20-EBK-ACC               | Version        |  |
| Order No.  | <a href="#">1346610000</a> | End bracket, , |  |
| GTIN (EAN) | 4050118151596              |                |  |
| Qty.       | 5 ST                       |                |  |

|            |                            |          |  |
|------------|----------------------------|----------|--|
| Type       | UR20-SM-ACC                | Version  |  |
| Order No.  | <a href="#">1339920000</a> | Cover, , |  |
| GTIN (EAN) | 4050118144727              |          |  |
| Qty.       | 20 ST                      |          |  |

### Blank



### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | PM 2.7/2.6 MC NE WS        | Version  |  |
| Order No.  | <a href="#">1323710000</a> | OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch |  |
| GTIN (EAN) | 4050118126778              | in mm (P): 3.50 Weidmueller, white                               |  |
| Qty.       | 960 ST                     |  |  |

### Custom printing



## UR20-FBC-EIP-V2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | PM 2.7/2.6 MC SDR          | Version  |  |
| Order No.  | <a href="#">1323700000</a> | OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch |  |
| GTIN (EAN) | 4050118126761              | in mm (P): 3.50 Weidmueller, To customer specification           |  |
| Qty.       | 192 ST                     |  |  |

### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | DEK 5/8-11.5 MC NE WS      | Version   |  |
| Order No.  | <a href="#">1341630000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |  |
| GTIN (EAN) | 4050118145946              | Weidmueller, white  |  |
| Qty.       | 500 ST                     |   |  |

### Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | DEK 5/8-11.5 MC SDR        | Version   |  |
| Order No.  | <a href="#">1341610000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |  |
| GTIN (EAN) | 4050118146059              | Weidmueller, To customer specification                    |  |
| Qty.       | 100 ST                     |   |  |


## UR20-FBC-EIP-V2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Accessories



#### System accessory

Discover a wide range of accessories for your u-remote system - the ideal addition to make your applications even more efficient and flexible.

### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | IE-USB-A-MICRO-1.8M        | Version                                 |  |
| Order No.  | <a href="#">1487980000</a> | USB cable, USB A, USB Micro, PVC, 1.8 m |  |
| GTIN (EAN) | 4050118298451              |   |  |
| Qty.       | 1 ST                       |   |  |

### Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | PZ 2.5 S                   | Version  |  |
| Order No.  | <a href="#">2903690000</a> | 0.14mm <sup>2</sup> , 2.5mm <sup>2</sup> , Trapezoidal crimp |  |
| GTIN (EAN) | 4099986027008              |  |  |
| Qty.       | 1 ST                       |  |  |