


**CAN SUB-D SK TERM PS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | SUB-D                      |
| Order No.  | <a href="#">1550590000</a> |
| Type       | CAN SUB-D SK TERM PS       |
| GTIN (EAN) | 4050118357134              |
| Qty.       | 1 items                    |

## CAN SUB-D SK TERM PS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 17 mm   | Depth (inches)  | 0.6693 inch |
| Height     | 54 mm   | Height (inches) | 2.126 inch  |
| Width      | 46 mm   | Width (inches)  | 1.811 inch  |
| Net weight | 85.36 g |                 |             |

### Temperatures

|          |                                   |
|----------|-----------------------------------|
| Humidity | Max. 75% at +25°C, non-condensing |
|----------|-----------------------------------|

### Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6al                                  |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 3cc1d9b1-0f2a-47ed-a501-ddcfcfaaf625 |

### Technical specifications for sub-D connector

|                              |                                   |                                |                   |
|------------------------------|-----------------------------------|--------------------------------|-------------------|
| Tightening torque            | 0.3 Nm                            | Housing main material          | ZnAl              |
| Humidity                     | Max. 75% at +25°C, non-condensing | Protection degree              | IP30              |
| Plugging cycles              | ≥ 200                             | Data rate                      | 1 Mbps            |
| Outgoing elbow               | 90°                               | Terminating resistor available | Yes               |
| BUS interface                | D-Sub 9-pole, Pin                 | Interlock                      | UNC4-40           |
| Temperature range of housing | -20...+70 °C                      | BUS PG interface               | D-Sub 9-pole, Pin |
| BUS, cable interface         | Screw connection                  | Programming interface          | Yes               |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001132    | ETIM 9.0    | EC001132    |
| ETIM 10.0   | EC001132    | ECLASS 14.0 | 27-44-03-02 |
| ECLASS 15.0 | 27-44-03-22 |             |             |