


**WQB WPD X05/3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), Plugged, grey, 135 A, Number of poles: 3, Pitch in mm (P): 35.60, Insulated: Yes, Width: 88.4 mm
Order No.	<a href="#">1561970000</a>
Type	WQB WPD X05/3
GTIN (EAN)	4050118367133
Qty.	20 items

## WQB WPD X05/3

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	19.6 mm	Depth (inches)	0.7717 inch
Height	14 mm	Height (inches)	0.5512 inch
Width	88.4 mm	Width (inches)	3.4803 inch
Net weight	19.9 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	grey
----------------	-------	--------	------

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
Type of mounting	Plugged		

## Dimensions

Pitch in mm (P)	35.60 mm
-----------------	----------

## General

Number of poles	3
-----------------	---

## Rating data

Nominal current	135 A
-----------------	-------

## Important note

Product information	Max. 135 A only possible with mid feed-in
---------------------	-------------------------------------------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		