


**WQB WPD X04/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), Plugged, grey, 135 A, Number of poles: 2, Pitch in mm (P): 31.50, Insulated: Yes, Width: 49.3 mm |
| Order No.  | <a href="#">1561980000</a>   |
| Type       | WQB WPD X04/2  |
| GTIN (EAN) | 4050118367317  |
| Qty.       | 20 items   |

## WQB WPD X04/2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 19.6 mm | Depth (inches)  | 0.7717 inch |
| Height     | 14 mm   | Height (inches) | 0.5512 inch |
| Width      | 49.3 mm | Width (inches)  | 1.9409 inch |
| Net weight | 11.4 g  |                 |             |

### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                |       |        |      |
|----------------|-------|--------|------|
| Basic material | Wemid | Colour | grey |
|----------------|-------|--------|------|

### System specifications

|         |                 |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

### Additional technical data

|                          |         |                     |                 |
|--------------------------|---------|---------------------|-----------------|
| Type of fixing           | Plugged | Installation advice | when screwed in |
| Explosion-tested version | No      | Type of mounting    | Plugged         |

### Dimensions

|                 |          |
|-----------------|----------|
| Pitch in mm (P) | 31.50 mm |
|-----------------|----------|

### General

|                 |   |                     |                 |
|-----------------|---|---------------------|-----------------|
| Number of poles | 2 | Installation advice | when screwed in |
|-----------------|---|---------------------|-----------------|

### Rating data

|               |       |                 |       |
|---------------|-------|-----------------|-------|
| Rated voltage | 400 V | Nominal current | 135 A |
|---------------|-------|-----------------|-------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |