


**WQB WPD X04/3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), Plugged, grey, 135 A, Number of poles: 3, Pitch in mm (P): 31.50, Insulated: Yes, Width: 80.2 mm |
| Order No.  | <a href="#">1561990000</a>   |
| Type       | WQB WPD X04/3  |
| GTIN (EAN) | 4050118367324  |
| Qty.       | 20 items   |

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 19.6 mm | Depth (inches)  | 0.7717 inch |
| Height     | 14 mm   | Height (inches) | 0.5512 inch |
| Width      | 80.2 mm | Width (inches)  | 3.1575 inch |
| Net weight | 18.6 g  |                 |             |

**Temperatures**

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

**Material data**

Basic material Wemid Colour grey

**System specifications**

Version Cross-connector

**Additional technical data**

|                          |         |                     |                 |
|--------------------------|---------|---------------------|-----------------|
| Type of fixing           | Plugged | Installation advice | when screwed in |
| Explosion-tested version | No      | Type of mounting    | Plugged         |

**Dimensions**

Pitch in mm (P) 31.50 mm

**General**

Number of poles 3 Installation advice when screwed in

**Rating data**

Nominal current 135 A

**Important note**

Product information Max. 135 A only possible with mid feed-in

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |