RSV1,6 ZE36 BK BX



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







Similar to illustration

For frequent load changes: the "trailer coupling" for plugin connectors.

The strain relief can do more than just relieve the strain on conductors:

Simply clip onto the plug and

- bundle conductors
- guide cables
- use as a connection and disconnection aid

No damage to the connecting points, clear, tidy wiring and easy to handle.

User advantages: permanent heavy-duty connections for harsh industrial environments and convenient operation ensure improved system availability.

General ordering data

PCB plug-in connector, Accessories, Strain relief,
black, Number of poles: 36
<u>1563000000</u>
RSV1,6 ZE36 BK BX
4008190187538
10 items
Вох



RSV1,6 ZE36 BK BX



Weidmüller Interface GmbH & Co. KG

27-46-04-02

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals			
ROHS	Conform		
Dimensions and weights			
Net weight	19.54 g		
Environmental Product Comp	pliance		
RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Material data			
	D.A.		
Insulating material	PA PAL 2011	Colour	black
Colour chart (similar)	RAL 9011	Moisture Level (MSL)	40.00
Contact material	Cu-alloy	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 ℃
Temperature range, installation, max.	100 °C		
Rated data acc. to IEC			
tested acc. to standard	IEC 60664-1, IEC 61984		
Packing			
Pookoging	Box	VPE length	184.00 mm
Packaging VPE width	115.00 mm	VPE height	91.00 mm
Important note		- U	,
•			
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the production be evaluated on request.		
Notes	\bullet Long term storage of the product with average temperature of 50 $^{\circ}\text{C}$ and maximum humidity 70%, 36 months		
Classifications			
FTIM C O	FC002042	ETIM 7 O	FC002042
ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 8.0 ETIM 10.0	EC002943 EC002943	ETIM 9.0 ECLASS 9.0	EC002943 27-44-04-92
	EC002943	ETIM 9.0	EC002943

ECLASS 13.0

ECLASS 15.0

2 Catalogue status / Drawings

ECLASS 14.0

27-46-04-02

27-46-04-02