

**HSS-HF 12.7-25.4EL B30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 12.7 - 25.4 mm, blue
Order No.	<a href="#">1562930000</a>
Type	HSS-HF 12.7-25.4EL B30M
GTIN (EAN)	4050118367720
Qty.	1 items

## HSS-HF 12.7-25.4EL B30M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.0591 inch
Width	40.5 mm	Width (inches)	1.5945 inch
Length	30000 mm	Length (inches)	1181.1 inch
Net weight	1355.2 g		

### Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	Width	40.5 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	blue	Halogen	No
Length	30000 mm	Basic material	Polyolefine
Printed characters	without	compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>
Operating temperature range	-55...105 °C	Number per roll	1

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	35 mm <sup>2</sup>	Conductor O.D., max.	25.4 mm
Conductor O.D., min.	12.7 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	12.7 - 25.4 mm
Cross-section for connected wire	35 - 120 mm <sup>2</sup>		

### Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

---

---

---

---

---

---

