

**RSV1,6 ZE12 BK BX****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



For frequent load changes: the "trailer coupling" for plug-in connectors.

The strain relief can do more than just relieve the strain on conductors:

Simply clip onto the plug and

- bundle conductors
- guide cables
- use as a connection and disconnection aid

No damage to the connecting points, clear, tidy wiring and easy to handle.

User advantages: permanent heavy-duty connections for harsh industrial environments and convenient operation ensure improved system availability.

**General ordering data**

Version	PCB plug-in connector, Accessories, Strain relief, black, Number of poles: 12
Order No.	<a href="#">1563300000</a>
Type	RSV1,6 ZE12 BK BX
GTIN (EAN)	4008190095871
Qty.	25 items
Product data	
Packaging	Box

**RSV1,6 ZE12 BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 10.64 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Material data**

Insulating material	PA	Colour	black
Colour chart (similar)	RAL 9011	Moisture Level (MSL)	
Contact material	Cu-alloy	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	100 °C		

**Rated data acc. to IEC**

tested acc. to standard IEC 60664-1, IEC 61984

**Packing**

Packaging	Box	VPE length	186.00 mm
VPE width	112.00 mm	VPE height	90.00 mm

**Important note**

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

**Classifications**

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-46-04-02
ECLASS 15.0	27-46-04-02		

## RSV1,6 ZE12 BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Natural



- CB cable ties for the fastening of cables and markers.
- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
  - IEC 62275: 2006-conformant
  - Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

### General ordering data

Type	CB 140/3,5 NC	Version	
Order No.	<a href="#">1278700000</a>		Cable ties, 3.5 x 140 mm, Polyamide 66, 180 N
GTIN (EAN)	4008190155759		
Qty.	9000 ST		