

**HSS 1.6-4.8 EL Y100M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 1.6 - 4.8 mm, yellow
Order No.	<a href="#">1563050000</a>
Type	HSS 1.6-4.8 EL Y100M
GTIN (EAN)	4050118367669
Qty.	1 items

## HSS 1.6-4.8 EL Y100M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Width	7.6 mm	Width (inches)	0.2992 inch
Length	100000 mm	Length (inches)	3937 inch
Net weight	650 g		

### Temperatures

Operating temperature range	-55...135 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	Width	7.6 mm
Operating temperature range, max.	135 °C	Operating temperature range, min.	-55 °C
Colour	yellow	Halogen	Yes
Length	100000 mm	Basic material	Polyolefine
Printed characters	without	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	Operating temperature range	-55...135 °C

### Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	4.8 mm
Conductor O.D., min.	1.6 mm	Rate of shrinkage	3:1
Recommended shrinking temperature	90 °C	Conductor O.D.	1.6 - 4.8 mm
Cross-section for connected wire	0.75 - 4 mm <sup>2</sup>		

### Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		