

## CLI C 02-3 GE/SW N CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow
Order No.	<a href="#">1568241663</a>
Type	CLI C 02-3 GE/SW N CD
GTIN (EAN)	4008190154424
Qty.	500 items

**CLI C 02-3 GE/SW N CD**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	3.5 mm	Depth (inches)	0.1378 inch
Height	3 mm	Height (inches)	0.1181 inch
Width	3.4 mm	Width (inches)	0.1339 inch
Net weight	0.06 g		

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Material colour according to resistance code	4		
Orientation of print	horizontal		
Type of printing	Standard		
Printing method	hot-embossing		
Version	CD		
Width	3.4 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-30 °C		
Colour	yellow		
Halogen	Yes		
Insulation cross-section, max.	3		
Basic material	PVC, soft, without Cadmium		
Colour of printing	black		
Printed characters	Upper-case letters		
Number of markers per packaging unit	Form of supply	Reel	
Recommended industries	Process, Machinery		
Number of markers per combination	1 Reel = Conductor and cable markers		
Operating temperature range	-30...80 °C		
Imprint	N		

**Conductor and cable markers**

Halogen	Yes	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.2 mm <sup>2</sup>	Conductor O.D., max.	3 mm
Conductor O.D., min.	1.3 mm	Conductor O.D.	1.3 - 3 mm
Cross-section for connected wire	0.2 - 1.5 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



Similar to illustration