

## CLI C 1-3 WS/SW J CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 2.5 - 5 mm, 3 x 4.2 mm, white
Order No.	<a href="#">1568251030</a>
Type	CLI C 1-3 WS/SW J CD
GTIN (EAN)	4032248441280
Qty.	500 items

## CLI C 1-3 WS/SW J CD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	3 mm	Height (inches)	0.1181 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Net weight	0.08 g		

## Temperatures

Operating temperature range -30...80 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## General data

Material colour according to resistance code 9

Orientation of print horizontal

Type of printing Standard

Printing method hot-embossing

Version CD

Width 4.2 mm

UL 94 flammability rating V-0

Operating temperature range, max. 80 °C

Operating temperature range, min. -30 °C

Colour white

Halogen Yes

Basic material PVC, soft, without Cadmium

Colour of printing black

Printed characters Upper-case letters

Number of markers per packaging unit Form of supply Reel

Recommended industries Process, Machinery

Number of markers per combination 1 Reel = Conductor and cable markers

Operating temperature range -30...80 °C

Imprint J

## Conductor and cable markers

Halogen Yes

Conductor cross-section, min. 1.5 mm<sup>2</sup>

Conductor O.D., min. 2.5 mm

Cross-section for connected wire 1.5 - 4 mm<sup>2</sup>Conductor cross-section, max. 4 mm<sup>2</sup>

Conductor O.D., max. 5 mm

Conductor O.D. 2.5 - 5 mm

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



Similar to illustration