

CLI C 1-3 GE/SW Å CD

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 2.5 - 5 mm, 3 x 4.2 mm, yellow
Order No.	1568251799
Type	CLI C 1-3 GE/SW Å CD
GTIN (EAN)	4032248443536
Qty.	500 items

CLI C 1-3 GE/SW Å CD

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	3 mm	Height (inches)	0.1181 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Net weight	0.08 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4
Orientation of print	horizontal
Type of printing	Standard
Printing method	hot-embossing
Version	CD
Width	4.2 mm
UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C
Colour	yellow
Halogen	Yes
Basic material	PVC, soft, without Cadmium
Colour of printing	black
Printed characters	Upper-case letters
Number of markers per packaging unit	Form of supply
Recommended industries	Reel
Process, Machinery	
Number of markers per combination	1 Reel = Conductor and cable markers
Operating temperature range	-30...80 °C
Imprint	Å

Conductor and cable markers

Conductor cross-section, max.	4 mm ²
Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm
Cross-section for connected wire	1.5 - 4 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

CLI C 1-3 GE/SW Å CD

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration