Data sheet

CLI C 2-4 GE/SW D CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow
Order No.	1568261643
Type	CLI C 2-4 GE/SW D CD
GTIN (EAN)	4008190037154
Qty.	250 items

Data sheet

CLI C 2-4 GE/SW D CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	0.22 g		

Temperatures

Operating temperature range	-30…80 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4		
Orientation of print	horizontal		
Type of printing	Standard		
Printing method	hot-embossing		
Version	CD		
Width	7 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-30 °C		
Colour	yellow		
Halogen	Yes		
Insulation cross-section, max.	10		
Basic material	PVC, soft, without Cadmium		
Colour of printing	black		
Printed characters	Upper-case letters		
Number of markers per packaging unit	Form of supply	Reel	
Recommended industries	Process, Machinery		
Number of markers per combination	1 Reel = Conductor and cable markers		
Operating temperature range	-30…80 °C		
Imprint	D		

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	16 mm²
Conductor cross-section, min.	2.5 mm²	Conductor O.D., max.	10 mm
Conductor O.D., min.	4 mm	Conductor O.D.	4 - 10 mm
Cross-section for connected wire	2.5 - 16 mm²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

CLI C 2-4 GE/SW D CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Similar to illustration