

CLI M 2-4 GE/SW 4 CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, yellow
Order No.	1568301514
Type	CLI M 2-4 GE/SW 4 CD
GTIN (EAN)	4008 190024987
Qty.	500 items

CLI M 2-4 GE/SW 4 CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	11.3 mm	Width (inches)	0.4449 inch
Net weight	0.13 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	
Orientation of print	horizontal	
Type of printing	Standard	
Printing method	hot-embossing	
Version	CD	
Width	11.3 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Colour	yellow	
Halogen	Yes	
Basic material	PVC, soft, without Cadmium	
Colour of printing	black	
Printed characters	Numbers	
Number of markers per packaging unit	Form of supply	Reel
Recommended industries	Process, Machinery	
Number of markers per combination	1 Reel = Conductor and cable markers	
Operating temperature range	-30...80 °C	
Imprint	4	

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 500 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



Similar to illustration

CLI M 2-4 GE/SW 4 CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Holders



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Type	CLI MH 110 HSTR	Version
Order No.	0189400000	CableLine, Accessories, 10 - 317 mm, 110 x 11.3 mm, black
GTIN (EAN)	4008190144784	
Qty.	100 ST	
Type	CLI MH 70 HSTR	Version
Order No.	0524400000	CableLine, Accessories, 10 - 317 mm, 70 x 11.3 mm, black
GTIN (EAN)	4008190075057	
Qty.	100 ST	