

## CLI M 2-4 GE/SW Q CD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, yellow
Order No.	<a href="#">1568301669</a>
Type	CLI M 2-4 GE/SW Q CD
GTIN (EAN)	4008190029135
Qty.	500 items

**CLI M 2-4 GE/SW Q CD**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	3 mm	Depth (inches)	0.1181 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	11.3 mm	Width (inches)	0.4449 inch
Net weight	0.13 g		

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Material colour according to resistance code	4		
Orientation of print	horizontal		
Type of printing	Standard		
Printing method	hot-embossing		
Version	CD		
Width	11.3 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-30 °C		
Colour	yellow		
Halogen	Yes		
Basic material	PVC, soft, without Cadmium		
Colour of printing	black		
Printed characters	Upper-case letters		
Number of markers per packaging unit	Form of supply	Reel	
Recommended industries	Process, Machinery		
Number of markers per combination	1 Reel = Conductor and cable markers		
Operating temperature range	-30...80 °C		
Imprint	Q		

**Conductor and cable markers**

Halogen	Yes	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 500 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



Similar to illustration