


**CLI M 2-4 BL/WS 6 CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI M identification markers are slid onto CLI MH carrier strips and secured my means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

**General ordering data**

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, blue
Order No.	<a href="#">1568301521</a>
Type	CLI M 2-4 BL/WS 6 CD
GTIN (EAN)	4008190964955
Qty.	500 items

## CLI M 2-4 BL/WS 6 CD

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	11.3 mm	Width (inches)	0.4449 inch
Net weight	0.15 g		

## Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Material colour according to resistance code	6	
Orientation of print	horizontal	
Type of printing	Standard	
Printing method	hot-embossing	
Version	CD	
Width	11.3 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Colour	blue	
Halogen	Yes	
Basic material	PVC, soft, without Cadmium	
Colour of printing	white	
Printed characters	Numbers	
Number of markers per packaging unit	Form of supply	Reel
Recommended industries	Process, Machinery	
Number of markers per combination	1 Reel = Conductor and cable markers	
Operating temperature range	-30...80 °C	
Imprint	6	

## Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire			16 - 500 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## CLI M 2-4 BL/WS 6 CD

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Holders



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

## General ordering data

Type	CLI MH 110 HSTR	Version
Order No.	<a href="#">0189400000</a>	CableLine, Accessories, 10 - 317 mm, 110 x 11.3 mm, black
GTIN (EAN)	4008190144784	
Qty.	100 ST	
Type	CLI MH 70 HSTR	Version
Order No.	<a href="#">0524400000</a>	CableLine, Accessories, 10 - 317 mm, 70 x 11.3 mm, black
GTIN (EAN)	4008190075057	
Qty.	100 ST	