

VG 36-MS68

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS (standard brass cable gland), Cable glands, straight, PG 36, 9 mm, OD min. 22 - OD max. 32 mm, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
Order No.	1569130000
Type	VG 36-MS68
GTIN (EAN)	4008190148263
Qty.	5 items

VG 36-MS68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	48 mm	Height (inches)	1.8898 inch
Length	57 mm	Length (inches)	2.2441 inch
Net weight	253.77 g		

Temperatures

Operating temperature -40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Certificate numbers cable gland

Certificate no. cable gland (GERMLLOYD)	E-14047	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260	Approval conditions	DNV, UL, cULus

General information

Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
O-Ring	NBR	Protection degree with GWDR	IP67, IP68 - 5 bar (30 min.)
Tightening torque	20 Nm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.59 mm
Halogen	Yes	AF size 1	50 mm
AF size 2	50 mm	AF size	50 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Cable gland	PG, PG 36
Basic material	Brass, nickel-plated	Seal insert	CR
Sealing	NBR	External thread	PG 36
Length of thread	9 mm	Torque for cap nut, max.	43.00 Nm
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	21.00 Nm
Torque for connecting adapter, min.	19.00 Nm	Torque for cap nut, min.	41.00 Nm
Clamp insert	Polyamide		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

VG 36-MS68

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG36-MS	Version
Order No.	1719220000	SKMU MS (brass locknut), Locknut, PG 36, 5 mm, Brass, nickel-plated
GTIN (EAN)	4008190352479	
Qty.	50 ST	

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG36-NP	Version
Order No.	1719610000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 36, Neoprene
GTIN (EAN)	4008190352875	
Qty.	20 ST	

Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG36-PO	Version
Order No.	1719510000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 36,
GTIN (EAN)	4008190352776	Polyethylene
Qty.	50 ST	