

## VG 29-K68

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, PG 29, 11 mm, OD min. 18 - OD max. 25 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">1569030000</a>
Type	VG 29-K68
GTIN (EAN)	4008190142872
Qty.	20 items

## VG 29-K68

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	41 mm	Height (inches)	1.6142 inch
Length	52 mm	Length (inches)	2.0472 inch
Net weight	34.8 g		

## Temperatures

Operating temperature -40 °C...100 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## Certificate numbers cable gland

Certificate no. cable gland (UL) E-199260 - BS 17  
 Approval conditions DNV, UL, cULus  
 Certificate no. cable gland (cULus) E-199260 - BS 17

## General information

Outer cable diameter, max.	25 mm	Outer cable diameter, min.	18 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	9 Nm
Silicone	No	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.59 mm	Halogen	Yes
AF size 1	42 mm	AF size	42 mm
Protection degree	IP67, IP68 - 5 bar (30 min.)	Cable gland	PG
Basic material	Polyamide 6	Seal insert	CR
External thread	PG 29	Length of thread	11 mm
Torque for cap nut, max.	10.50 Nm	Torque for lock nut, min.	8.50 Nm
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	9.50 Nm
Torque for connecting adapter, min.	8.50 Nm	Torque for cap nut, min.	9.50 Nm
Torque for lock nut, max.	9.50 Nm		

## Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		