

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, PG 36, 13 mm, OD min. 22 - OD max. 32 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	1569040000
Type	VG 36-K68
GTIN (EAN)	4008190024833
Qty.	10 items

VG 36-K68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	51.5 mm	Height (inches)	2.0276 inch
Length	64.5 mm	Length (inches)	2.5394 inch
Net weight	66.4 g		

Temperatures

Operating temperature -40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

Certificate no. cable gland (UL)	E-199260 - BS 18	Certificate no. cable gland (cULus)	E-199260 - BS 18
Approval conditions	DNV, UL, cULus		

General information

Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	11 Nm
Silicone	No	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.59 mm	Halogen	Yes
AF size 1	53 mm	AF size	53 mm
Protection degree	IP67, IP68 - 5 bar (30 min.)	Cable gland	PG
Basic material	Polyamide 6	Seal insert	CR
External thread	PG 36	Length of thread	13 mm
Torque for cap nut, max.	16.50 Nm	Torque for lock nut, min.	10.50 Nm
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	11.50 Nm
Torque for connecting adapter, min.	10.50 Nm	Torque for cap nut, min.	15.50 Nm
Torque for lock nut, max.	11.50 Nm		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		