

**WQB A/24**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, black, 24 A, Number of poles: 24, Pitch in mm (P): 5.10, Insulated: Yes, Width: 123.22 mm
Order No.	<a href="#">1579000000</a>
Type	WQB A/24
GTIN (EAN)	4008190134211
Qty.	20 items

## WQB A/24

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.0984 inch
Height	23.5 mm	Height (inches)	0.9252 inch
Width	123.22 mm	Width (inches)	4.8512 inch
Net weight	7.18 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...25 °C
Continuous operating temp., max.	70 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	tinned copper	Colour	black
----------------	---------------	--------	-------

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

## Dimensions

Pitch in mm (P)	5.10 mm
-----------------	---------

## General

Number of poles	24	Installation advice	Feed-through (bushing), Direct mounting
-----------------	----	---------------------	--

## Rating data

Rated voltage	800 V	Nominal current	24 A
---------------	-------	-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		