

WQB B/10

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, black, 24 A, Number of poles: 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.26 mm |
| Order No. | 1579050000 |
| Type | WQB B/10 |
| GTIN (EAN) | 4008190094508 |
| Qty. | 20 items |

WQB B/10

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 2.5 mm | Depth (inches) | 0.0984 inch |
| Height | 23.5 mm | Height (inches) | 0.9252 inch |
| Width | 48.26 mm | Width (inches) | 1.9 inch |
| Net weight | 3.33 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...25 °C |
| Continuous operating temp., max. | 70 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|---------------|--------|-------|
| Basic material | tinned copper | Colour | black |
|----------------|---------------|--------|-------|

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | | |

Dimensions

| | | | |
|-----------------|---------|--------------|-------|
| Pitch in mm (P) | 5.10 mm | TS 35 offset | 54 mm |
|-----------------|---------|--------------|-------|

General

| | | | |
|-----------------|----|---------------------|-----------------|
| Number of poles | 10 | Installation advice | Direct mounting |
|-----------------|----|---------------------|-----------------|

Rating data

| | | | |
|---------------|-------|-----------------|------|
| Rated voltage | 800 V | Nominal current | 24 A |
|---------------|-------|-----------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |