

## SL FLA 3.8/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Product image



Similar to illustration

Effective: the link between LED and front panel.

Floodlight indicators allow users to monitor the switching states without requiring a special design: optical plastic directs the light from standard LEDs around a bend into the connectors or through the front plate.

The fibre-optic elements are simply clipped behind the relevant 90° bend male connectors (90° outlet direction). Versions with different incoming light beam heights achieve maximum light efficiency for LEDs with different designs or heights.

The advantages compared to conventional solutions:

- No additional LED circuit board required behind the front panel
- No "long-legged" LEDs with separate mounting required
- Bent fibre-optic cable line for maximum light efficiency
- Uncomplicated front plate bore holes due to circular shape of outgoing light beam
- Easy to maintain correct clearance and creepage distance
- Can be partitioned for smaller pole numbers

The result: simplified manufacturing process, reduced costs and simplified design

## General ordering data

|              |  |
|--------------|--|
| Version      | PCB plug-in connector, Accessories, Flood-light display, Transparent, Number of poles: 1 |
| Order No.    | <a href="#">1580110000</a>   |
| Type         | SL FLA 3.8/1   |
| GTIN (EAN)   | 4008190050740  |
| Qty.         | 100 items  |
| Product data |  |
| Packaging    | Box  |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 0.46 g |
|------------|--------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                                       |                         |                                       |             |
|---------------------------------------|-------------------------|---------------------------------------|-------------|
| Insulating material                   | Polymethyl methacrylate | Colour                                | Transparent |
| Colour chart (similar)                | -                       | Moisture Level (MSL)                  |             |
| Contact material                      | Cu-alloy                | Storage temperature, min.             | -40 °C      |
| Storage temperature, max.             | 70 °C                   | Operating temperature, min.           | -50 °C      |
| Operating temperature, max.           | 100 °C                  | Temperature range, installation, min. | -25 °C      |
| Temperature range, installation, max. | 100 °C                  |                                       |             |

### Rated data acc. to IEC

|                         |                        |
|-------------------------|------------------------|
| tested acc. to standard | IEC 60664-1, IEC 61984 |
|-------------------------|------------------------|

### Packing

|           |          |            |          |
|-----------|----------|------------|----------|
| Packaging | Box      | VPE length | 91.00 mm |
| VPE width | 72.00 mm | VPE height | 42.00 mm |

### Important note

|                |  |
|----------------|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
| Notes          | <ul style="list-style-type: none"> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul>   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002943    | ETIM 9.0    | EC002943    |
| ETIM 10.0   | EC002943    | ECLASS 14.0 | 27-46-04-04 |
| ECLASS 15.0 | 27-46-04-04 |             |             |