SLA BB14 OR



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Minor component, major effect:

Clip-on attachment elements increase the mechanical resilience of the whole plug connection by

- securing the male connectors to the circuit board
- providing a vibration-proof connection between the sockets and the male connectors

Clip-on or pre-assembled - always the right solution:

- · Hard-wearing, precise fitting dovetail joint
- · Hard-wearing metal threaded inserts
- Suitable for all outlet directions

Maximum stability, minimum effort:

- Extremely resilient for frequent fastening operations
- Complete set for easy selection

The result: soldering points, contacts and overall module are more resilient against mechanical stress such as vibrations and tensile loads.

General ordering data

Version	PCB plug-in connector, Accessories, Mounting	
	block, orange, Number of poles: 0	
Order No.	<u>1594200000</u>	
Туре	SLA BB14 OR	
GTIN (EAN)	4008190184988	
Qty.	20 items	
Product data		
Packaging	Box	

Catalogue status / Drawings



SLA BB14 OR



Weidmüller Interface GmbH & Co. KG

27-46-04-05

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals				
Paula				
ROHS	Conform			
Dimensions and weights				
Depth	22.16 mm	Depth (inches)	0.8724 inch	
Height	26.68 mm	Height (inches)	1.0504 inch	
Nidth	5.08 mm	Width (inches)	0.2 inch	
Net weight	2.86 g	width (inches)	0.2 IIICII	
Environmental Product Comp	oliance			
RoHS Compliance Status	Compliant with exemption			
RoHS Exemption (if applicable/known) 6c			
REACH SVHC	Lead 7439-92-1			
SCIP	00c92aa4-198d-4f32-82d1-4ccab9233b4d			
Material data				
	DDT OF	Colour		
Insulating material	PBT GF	Colour	orange	
Colour chart (similar)	RAL 2000	Moisture Level (MSL)		
JL 94 flammability rating	V-0	Contact material	Cu-alloy	
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C	
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C	
Temperature range, installation, min.	-25 ℃	Temperature range, installation, max.	100 °C	
Rated data acc. to IEC				
tested acc. to standard	IEC 60664-1, IEC 6198	34		
Packing				
Packaging	Box	VPE length	85.00 mm	
VPE width	79.00 mm	VPE height	49.00 mm	
Important note	,		'	
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the producan be evaluated on request.			
Votes	 Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months 			
Classifications				
ETIM 6.0	EC002943	ETIM 7.0	EC002943	
	EC002943 EC002943	ETIM 7.0 ETIM 9.0		
ETIM 8.0			EC002943	
ETIM 10.0 ECLASS 9.1	EC002943 27-44-04-92	ECLASS 9.0 ECLASS 10.0	27-44-04-92	
	, ,-44-114-4 /	ECLASS TU.U	27-44-04-92	
ECLASS 9.1 ECLASS 11.0	27-46-04-05	ECLASS 12.0	27-46-04-05	

Creation date 29.11.2025 08:23:26 MEZ

ECLASS 13.0

ECLASS 15.0

Catalogue status / Drawings 2

ECLASS 14.0

27-46-04-05

27-46-04-05