

**SAKH 35 EP/SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |  |
|------------|--|
| Version    | Feed-through terminal block, Screw connection, black, 35 mm <sup>2</sup> , 125 A, 1000 V, Number of connections: 2 |
| Order No.  | <a href="#">1596240000</a>   |
| Type       | SAKH 35 EP/SW  |
| GTIN (EAN) | 4008190093570  |
| Qty.       | 20 items   |

**SAKH 35 EP/SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



|                       |                            |
|-----------------------|----------------------------|
| ROHS                  | Conform                    |
| UL File Number Search | <a href="#">UL Website</a> |
| Certificate No. (UR)  | E60693                     |

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 87.5 mm | Depth (inches)  | 3.4449 inch |
| Height     | 74 mm   | Height (inches) | 2.9134 inch |
| Width      | 23 mm   | Width (inches)  | 0.9055 inch |
| Net weight | 141.7 g |                 |             |

**Temperatures**

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 160 °C        |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Material data**

|                           |                 |        |       |
|---------------------------|-----------------|--------|-------|
| Basic material            | Epoxy resin, EP | Colour | black |
| UL 94 flammability rating | V-0             |        |       |

**Rating data IECEx/ATEX**

|                                |                    |                                 |                    |
|--------------------------------|--------------------|---------------------------------|--------------------|
| Certificate No. (ATEX)         | TUEV18ATEX8206U    | Certificate No. (IECEX)         | IECEXTUR18.0016U   |
| Max. voltage (ATEX)            | 1100 V             | Current (ATEX)                  | 125 A              |
| Wire cross section max. (ATEX) | 35 mm <sup>2</sup> | Max. voltage (IECEX)            | 1100 V             |
| Current (IECEX)                | 125 A              | Wire cross section max. (IECEX) | 35 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex eb II C Gb      | Ex 2014/34/EU label             | II 2 G D           |

**System specifications**

|                                     |   |                               |    |
|-------------------------------------|---|-------------------------------|----|
| Version                             | Screw connection, One end without connector | End cover plate required      | No |
| Number of potentials                | 1   | Number of levels              | 1  |
| Number of clamping points per level | 2   | Number of potentials per tier | 1  |
| Levels cross-connected internally   | No  | PE connection                 | No |
| Mounting rail                       | TS 32                                       | N-function                    | No |
| PE function                         | No  | PEN function                  | No |

## SAKH 35 EP/SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Additional technical data

|                          |        |                             |         |
|--------------------------|--------|-----------------------------|---------|
| Open sides               | closed | Number of similar terminals | 1       |
| Explosion-tested version | Yes    | Type of mounting            | Snap-on |

### CSA rating data

|                               |        |                       |                |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 2 AWG  | Voltage size C (CSA)  | 1500 V         |
| Current size C (CSA)          | 125 A  | Certificate No. (CSA) | 200039-1501714 |
| Voltage size B (CSA)          | 600 V  | Current size B (CSA)  | 125 A          |
| Voltage size D (CSA)          | 600 V  | Current size D (CSA)  | 5 A            |
| Wire cross section min. (CSA) | 12 AWG |                       |                |

### Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

### Conductors for clamping (rated connection)

|   |                     |   |                    |
|---|---------------------|---|--------------------|
| Gauge to IEC 60947-1  | B8                  | Wire connection cross section AWG, max.   | AWG 2              |
| Connection direction  | on side             | Tightening torque, max.   | 4.4 Nm             |
| Tightening torque, min.   | 2.5 Nm              | Stripping length  | 18 mm              |
| Type of connection  | Screw connection    | Number of connections   | 2                  |
| Clamping range, max.  | 50 mm <sup>2</sup>  | Clamping range, min.  | 4 mm <sup>2</sup>  |
| Clamping screw  | M 6                 | Blade size  | 6.5 x 1.2 mm       |
| Wire connection cross section AWG, min.   | AWG 12              | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 35 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 4 mm <sup>2</sup>   | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 35 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 4 mm <sup>2</sup>   | Wire connection cross section, finely stranded, max.                                    | 35 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, min.                                    | 4 mm <sup>2</sup>   | Connection cross-section, stranded, max.  | 50 mm <sup>2</sup> |
| Connection cross-section, stranded, min.  | 4 mm <sup>2</sup>   | Twin wire-end ferrules, max.  | 16 mm <sup>2</sup> |
| Twin wire-end ferrules, min.  | 1.5 mm <sup>2</sup> | Wire connection cross-section, solid core, max.   | 16 mm <sup>2</sup> |
| Wire connection cross-section, solid core, min.   | 4 mm <sup>2</sup>   | Connection cross-section, finely stranded, min.   | 4 mm <sup>2</sup>  |

### General

|   |               |   |        |
|---|---------------|---|--------|
| Wire connection cross section AWG, max. | AWG 2         | Wire connection cross section AWG, min. | AWG 12 |
| Standards                               | IEC 60947-7-1 | Mounting rail                           | TS 32  |

### Rating data

|  |                    |                                 |               |
|--|--------------------|---------------------------------|---------------|
| Rated cross-section                          | 35 mm <sup>2</sup> | Rated voltage                   | 1000 V        |
| Rated DC voltage                             | 1000 V             | Nominal current                 | 125 A         |
| Current at maximum wires                     | 150 A              | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 0.26 mΩ            | Rated impulse withstand voltage | 8 kV          |
| Power loss in accordance with IEC 60947-7-x  | 4.00 W             | Pollution severity              | 3             |

**SAKH 35 EP/SW****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Technical data****UL rating data**

|                     |       |                              |        |
|---------------------|-------|------------------------------|--------|
| Voltage size B (UR) | 600 V | Wire cross section min. (UR) | 12 AWG |
| Current size B (UR) | 115 A | Wire cross section max. (UR) | 2 AWG  |
| Current size D (UR) | 5 A   | Current size C (UR)          | 115 A  |
| Voltage size C (UR) | 600 V | Certificate No. (UR)         | E60693 |
| Voltage size D (UR) | 600 V |                              |        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-01 |
| ECLASS 15.0 | 27-25-01-01 |             |             |

## SAKH 35 EP/SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

## Accessories

www.weidmueller.com

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | QL 2 SAK35                 | Version  |
| Order No.  | <a href="#">0123600000</a> | Cross-connector (terminal), when screwed in, grey, 99 A, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: No, Width: 27.8 mm  |
| GTIN (EAN) | 4008190092566              |  |
| Qty.       | 20 ST                      |  |
| Type       | QL 3 SAK35                 | Version  |
| Order No.  | <a href="#">0123700000</a> | Cross-connector (terminal), when screwed in, grey, 99 A, Number of poles: 3, Pitch in mm (P): 18.00, Insulated: No, Width: 45.8 mm |
| GTIN (EAN) | 4008190182526              |  |
| Qty.       | 20 ST                      |  |

## Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | QL 4 SAK35                 | Version  |
| Order No.  | <a href="#">0123800000</a> | Cross-connector (terminal), when screwed in, grey, 99 A, Number of poles: 4, Pitch in mm (P): 8.00, Insulated: No, Width: 63.8 mm    |
| GTIN (EAN) | 4008190165390              |  |
| Qty.       | 20 ST                      |  |
| Type       | QL 10 SAK35                | Version  |
| Order No.  | <a href="#">0338600000</a> | Cross-connector (terminal), when screwed in, grey, 99 A, Number of poles: 10, Pitch in mm (P): 18.00, Insulated: No, Width: 171.4 mm |
| GTIN (EAN) | 4008190106133              |  |
| Qty.       | 20 ST                      |  |

## SAKH 35 EP/SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | BFSC M4X30                 | Version  |  |
| Order No.  | <a href="#">0267100000</a> | Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7 mm, Height: 30 mm |  |
| GTIN (EAN) | 4008190187897              |  |  |
| Qty.       | 50 ST                      |  |  |

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | VH 17/8.2/5.2              | Version   |  |
| Order No.  | <a href="#">0267000000</a> | Connecting sleeve (terminal), when screwed in, Width: 8 mm, Height: 8 mm, Depth: 17 mm, Number of poles: 1, Cu Zn |  |
| GTIN (EAN) | 4008190146986              |   |  |
| Qty.       | 50 ST                      |   |  |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## SAKH 35 EP/SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6.5 MC NE WS         | Version   |
| Order No.  | <a href="#">1609840000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190203429              | Weidmueller, white  |
| Qty.       | 900 ST                     |   |

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6.5 MC SDR           | Version   |
| Order No.  | <a href="#">1609850000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190456610              | Weidmueller, To customer specification                      |
| Qty.       | 180 ST                     |   |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/8 MC NE WS           | Version   |
| Order No.  | <a href="#">1856740000</a> | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248400850              | Weidmueller, white  |
| Qty.       | 800 ST                     |   |

## SAKH 35 EP/SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Accessories

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/5 MC NE WS           | Version |   |
| Order No.  | <a href="#">1609801044</a> |         | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              |         | Weidmueller, white  |
| Qty.       | 1000 ST                    |         |   |

## Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## General ordering data

|            |                            |         |                                      |
|------------|----------------------------|---------|--------------------------------------|
| Type       | KISC M3X20.5/10 EK4        | Version |                                      |
| Order No.  | <a href="#">0303000000</a> |         | Clamping yoke, Mounting screw, Steel |
| GTIN (EAN) | 4008190163686              |         |                                      |
| Qty.       | 100 ST                     |         |                                      |

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | VH 12/4.9/3.3              | Version |   |
| Order No.  | <a href="#">0249000000</a> |         | Connecting sleeve (terminal), when screwed in, Width: 4.9 mm, |
| GTIN (EAN) | 4008190129507              |         | Height: 4.9 mm, Depth: 12 mm, Number of poles: 1, Copper      |
| Qty.       | 100 ST                     |         |   |

## SAKH 35 EP/SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

|            |                            |                                    |  |
|------------|----------------------------|------------------------------------|--|
| Type       | KISC M3X20 SAK10 CU5       | Version                            |  |
| Order No.  | <a href="#">0377100000</a> | SAK Series, Mounting screw, Copper |  |
| GTIN (EAN) | 4008190060350              |                                    |  |
| Qty.       | 100 ST                     |                                    |  |

### Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### General ordering data

|            |                            |                                |  |
|------------|----------------------------|--------------------------------|--|
| Type       | PS 4 F.STB 4               | Version                        |  |
| Order No.  | <a href="#">0299600000</a> | Test adapter (terminal), 230 V |  |
| GTIN (EAN) | 4008190074043              |                                |  |
| Qty.       | 20 ST                      |                                |  |
| Type       | STB 17/D6/4/M4 SAKC10      | Version                        |  |
| Order No.  | <a href="#">0147100000</a> | SAK Series, Socket             |  |
| GTIN (EAN) | 4008190183042              |                                |  |
| Qty.       | 50 ST                      |                                |  |

## SAKH 35 EP/SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/8 MC SDR             | Version |   |
| Order No.  | <a href="#">1856750000</a> |         | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248400867              |         | Weidmueller, To customer specification                    |
| Qty.       | 160 ST                     |         |   |

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/8 PLUS MC NE WS      | Version |   |
| Order No.  | <a href="#">1046350000</a> |         | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248782055              |         | Weidmueller, white  |
| Qty.       | 800 ST                     |         |   |

## SAKH 35 EP/SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/8 PLUS MC SDR        | Version |   |
| Order No.  | <a href="#">1046370000</a> |         | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 |
| GTIN (EAN) | 4032248782079              |         | Weidmueller, To customer specification                    |
| Qty.       | 160 ST                     |         |   |

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | DEK 5/8 MM WS              | Version |  |
| Order No.  | <a href="#">2007130000</a> |         | Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392012              |         |  |
| Qty.       | 500 ST                     |         |  |

## SAKH 35 EP/SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Marker holder




The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 ST                     |                            |

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 ST                     |                            |

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WEW 32/1 LCP/NA            | Version  |
| Order No.  | <a href="#">1067660000</a> | End bracket, Light Grey, TS 32, V-0, Wemid, Width: 12.2 mm, 130 °C |
| GTIN (EAN) | 4008190072353              |  |
| Qty.       | 50 ST                      |  |