


**SAKK 4 KER/WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |   |
|------------|---|
| Version    | Feed-through terminal block, Screw connection, white, 4 mm <sup>2</sup> , 32 A, 800 V, Number of connections: 2 |
| Order No.  | <a href="#">1598080000</a>  |
| Type       | SAKK 4 KER/WS   |
| GTIN (EAN) | 4008190020729   |
| Qty.       | 25 items  |

**SAKK 4 KER/WS**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



|                           |                            |
|---------------------------|----------------------------|
| ROHS                      | Conform                    |
| UL File Number Search     | <a href="#">UL Website</a> |
| Certificate No. (UR)      | E60693                     |
| Certificate No. (cURusEX) | E184763                    |

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 53 mm   | Depth (inches)  | 2.0866 inch |
| Height     | 40 mm   | Height (inches) | 1.5748 inch |
| Width      | 8 mm    | Width (inches)  | 0.315 inch  |
| Net weight | 31.56 g |                 |             |

**Temperatures**

|                                  |                |                                  |                 |
|----------------------------------|----------------|----------------------------------|-----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -60 °C...205 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 250 °C          |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Material data**

|                           |         |        |       |
|---------------------------|---------|--------|-------|
| Basic material            | Ceramic | Colour | white |
| UL 94 flammability rating | None    |        |       |

**Rating data IECEX/ATEX**

|                                |                   |                                 |                   |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | TUEV18ATEX8208U   | Certificate No. (IECEX)         | IECEXTUR18.0018U  |
| Max. voltage (ATEX)            | 440 V             | Current (ATEX)                  | 32 A              |
| Wire cross section max. (ATEX) | 6 mm <sup>2</sup> | Max. voltage (IECEX)            | 440 V             |
| Current (IECEX)                | 32 A              | Wire cross section max. (IECEX) | 6 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex eb II C Gb     | Ex 2014/34/EU label             | II 2 G D          |

**System specifications**

|                                     |   |                               |     |
|-------------------------------------|---|-------------------------------|-----|
| Version                             | Screw connection, for screwable cross-connection, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1   | Number of levels              | 1   |
| Number of clamping points per level | 2   | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No  | PE connection                 | No  |
| Mounting rail                       | TS 32   | N-function                    | No  |
| PE function                         | No  | PEN function                  | No  |

## SAKK 4 KER/WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Additional technical data

|                     |                 |                             |     |
|---------------------|-----------------|-----------------------------|-----|
| Open sides          | right           | Number of similar terminals | 1   |
| Installation advice | Direct mounting | Explosion-tested version    | Yes |
| Type of mounting    | Snap-on         |                             |     |

### CSA rating data

|                               |        |                       |           |
|-------------------------------|--------|-----------------------|-----------|
| Wire cross section max. (CSA) | 10 AWG | Voltage size C (CSA)  | 600 V     |
| Current size C (CSA)          | 36 A   | Certificate No. (CSA) | 12400-290 |
| Wire cross section min. (CSA) | 26 AWG |                       |           |

### Conductors for clamping (additional connection)

|  |                  |
|--|------------------|
| Connection type, additional connection | Screw connection |
|--|------------------|

### Conductors for clamping (rated connection)

|   |                      |   |                      |
|---|----------------------|---|----------------------|
| Gauge to IEC 60947-1  | A4                   | Wire connection cross section AWG, max.   | AWG 10               |
| Connection direction  | on side              | Tightening torque, max.   | 0.5 Nm               |
| Tightening torque, min.   | 0.5 Nm               | Stripping length  | 10 mm                |
| Type of connection  | Screw connection     | Number of connections   | 2                    |
| Clamping range, max.  | 6 mm <sup>2</sup>    | Clamping range, min.  | 0.33 mm <sup>2</sup> |
| Clamping screw  | M 3                  | Blade size  | 0.6 x 3.5 mm         |
| Wire connection cross section AWG, min.   | AWG 22               | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm <sup>2</sup>    |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.33 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>    |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.33 mm <sup>2</sup> | Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    |
| Wire connection cross section, finely stranded, min.                                    | 0.33 mm <sup>2</sup> | Connection cross-section, stranded, max.  | 4 mm <sup>2</sup>    |
| Connection cross-section, stranded, min.  | 0.33 mm <sup>2</sup> | Twin wire-end ferrules, max.  | 2.5 mm <sup>2</sup>  |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup>  | Torque level with DMS electric screwdriver  | 2                    |
| Wire connection cross-section, solid core, max.   | 6 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.   | 0.33 mm <sup>2</sup> |
| Connection cross-section, finely stranded, min.   | 0.33 mm <sup>2</sup> |   |                      |

### General

|   |        |                     |                 |
|---|--------|---------------------|-----------------|
| Wire connection cross section AWG, max. | AWG 10 | Installation advice | Direct mounting |
| Wire connection cross section AWG, min. | AWG 22 | Standards           | IEC 60947-7-1   |
| Mounting rail                           | TS 32  |                     |                 |

### Rating data

|  |                   |                                 |               |
|--|-------------------|---------------------------------|---------------|
| Rated cross-section                          | 4 mm <sup>2</sup> | Rated voltage                   | 800 V         |
| Rated DC voltage                             | 800 V             | Nominal current                 | 32 A          |
| Current at maximum wires                     | 41 A              | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1 mΩ              | Rated impulse withstand voltage | 8 kV          |

## SAKK 4 KER/WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

|   |        |                    |   |
|---|--------|--------------------|---|
| Power loss in accordance with IEC 60947-7-x | 1.02 W | Pollution severity | 3 |
|---|--------|--------------------|---|

### UL rating data

|   |        |   |        |
|---|--------|---|--------|
| Conductor size Factory wiring max. (UR) | 12 AWG | Current size C (UR)                     | 30 A   |
| Voltage size C (UR)                     | 600 V  | Conductor size Factory wiring min. (UR) | 26 AWG |
| Certificate No. (UR)                    | E60693 | Conductor size Field wiring min. (UR)   | 26 AWG |
| Conductor size Field wiring max. (UR)   | 12 AWG |   |        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-01 |
| ECLASS 15.0 | 27-25-01-01 |             |             |

## SAKK 4 KER/WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | QL 2 SAKK4                 | Version   |
| Order No.  | <a href="#">9502540000</a> | Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: No, Width: 13.9 mm |
| GTIN (EAN) | 4008190550530              |   |
| Qty.       | 100 ST                     |   |

## Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | QL 4 SAKK4                 | Version   |
| Order No.  | <a href="#">9502560000</a> | Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 4, Pitch in mm (P): 8.00, Insulated: No, Width: 29.7 mm |
| GTIN (EAN) | 4008190550554              |   |
| Qty.       | 50 ST                      |   |

## End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | AP SAKK4/10 KER/WS         | Version  |
| Order No.  | <a href="#">9502630000</a> | End plate for terminals, white, Height: 40 mm, Width: 3 mm, V-0, Ceramic, Snap-on: Yes |
| GTIN (EAN) | 4008190047290              |  |
| Qty.       | 10 ST                      |  |

## SAKK 4 KER/WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | VH 13.5/4.9/3.3 NI         | Version   |  |
| Order No.  | <a href="#">9502580000</a> | Connecting sleeve (terminal), when screwed in, Width: 4.9 mm, |  |
| GTIN (EAN) | 4008190550578              | Height: 13.5 mm, Depth: 4.9 mm, Number of poles: 1, Cu Zn     |  |
| Qty.       | 100 ST                     |   |  |

## Disconnect plugs




In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## General ordering data

|            |                            |                                      |  |
|------------|----------------------------|--------------------------------------|--|
| Type       | KISC M3X20.5/10 EK4        | Version                              |  |
| Order No.  | <a href="#">0303000000</a> | Clamping yoke, Mounting screw, Steel |  |
| GTIN (EAN) | 4008190163686              |                                      |  |
| Qty.       | 100 ST                     |                                      |  |

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | MEW 1/32                   | Version   |  |
| Order No.  | <a href="#">0445600000</a> | End bracket, grey, TS 32, None, Steel, Width: 10.5 mm, 100 °C |  |
| GTIN (EAN) | 4008190178093              |   |  |
| Qty.       | 20 ST                      |   |  |

### Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/5 MC SDR             | Version |   |
| Order No.  | <a href="#">1609810000</a> |         | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190456597              |         | Weidmueller, To customer specification                    |
| Qty.       | 200 ST                     |         |   |

### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/5 MC NE WS           | Version |   |
| Order No.  | <a href="#">1609801044</a> |         | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              |         | Weidmueller, white  |
| Qty.       | 1000 ST                    |         |   |

## SAKK 4 KER/WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw. The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | SCHT 7                     | Version   |  |
| Order No.  | <a href="#">0517960000</a> | SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00 |  |
| GTIN (EAN) | 4008190001742              | Weidmueller, white  |  |
| Qty.       | 20 ST                      |   |  |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | DEK 5/6.5 MC NE WS         | Version   |  |
| Order No.  | <a href="#">1609840000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |  |
| GTIN (EAN) | 4008190203429              | Weidmueller, white  |  |
| Qty.       | 900 ST                     |   |  |

## SAKK 4 KER/WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

## Accessories

www.weidmueller.com

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6.5 MC SDR           | Version   |
| Order No.  | <a href="#">1609850000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190456610              | Weidmueller, To customer specification                      |
| Qty.       | 180 ST                     |   |

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6.5 PLUS MC NE GE    | Version   |
| Order No.  | <a href="#">1364020000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4050118166057              | Weidmueller, yellow   |
| Qty.       | 900 ST                     |   |
| Type       | DEK 5/6.5 PLUS MC NE WS    | Version   |
| Order No.  | <a href="#">1046340000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248782048              | Weidmueller, white  |
| Qty.       | 900 ST                     |   |

## SAKK 4 KER/WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | DEK 5/6.5 PLUS MC SDR      | Version |   |
| Order No.  | <a href="#">1046360000</a> |         | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248782062              |         | Weidmueller, To customer specification                      |
| Qty.       | 180 ST                     |         |   |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |         |                            |
|------------|----------------------------|---------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version |                            |
| Order No.  | <a href="#">1805490000</a> |         | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |         |                            |
| Qty.       | 100 ST                     |         |                            |
| Type       | BZT 1 ZA WS 10/5           | Version |                            |
| Order No.  | <a href="#">1805520000</a> |         | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |         |                            |
| Qty.       | 100 ST                     |         |                            |

## SAKK 4 KER/WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | QL 3 SAKK4                 | Version   |  |
| Order No.  | <a href="#">9502550000</a> | Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 3, Pitch in mm (P): 8.00, Insulated: No, Width: 21.8 mm |  |
| GTIN (EAN) | 4008190550547              |   |  |
| Qty.       | 100 ST                     |   |  |

## Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | QL 10 SAKK4                | Version  |  |
| Order No.  | <a href="#">9502570000</a> | Cross-connector (terminal), when screwed in, grey, 41 A, Number of poles: 10, Pitch in mm (P): 6.00, Insulated: No, Width: 77.1 mm |  |
| GTIN (EAN) | 4008190550561              |  |  |
| Qty.       | 20 ST                      |  |  |