
CLI F 1-20 WS/GE



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com









Similar to illustration

The Weidmüller range of conductor and cable marker products provides users with solutions for a wide variety of applications. The field of application ranges from thin conductors to cables with large outside diameters. The product range includes combination systems with individual tags, transparent sleeves and markers which can be fastened with cable ties. Open and closed markers, as well as printed or blank markers for individual labelling are available. Weidmüller's halogen-free and low-emission conductor markers are in compliance with European standards as well as with the in-house standards of well-known plant manufacturers. Markers for conductors and cables - Systems are available for:

- Clipping on pre-printed markers to suit individual labelling requirements
- Labelling with characters from a standard character set
- Combining individual, pre-printed characters to form a character code
- Customer labelling with SMark laser, PrintJet, MCP Plus plotter, MC-Mobilo, laser printer (DIN A4 format), thermal transfer printer or STI pen

A selection of samples can be found in the Weidmüller conductor marker sample bag, order No. 1640420000.

General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317
	mm, 20 x 4 mm, white
Order No.	<u>1600740000</u>
Туре	CLI F 1-20 WS/GE
GTIN (EAN)	4008190118402
Qty.	10 items

1

Catalogue status / Drawings



CLI F 1-20 WS/GE



Weidmüller Interface GmbH & Co. KG

27-40-04-01

27-28-11-02

27-28-11-02

2

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals			
ROHS	Conform		
	Conform		
Dimensions and weights			
Height	20 mm	Height (inches)	0.7874 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	18.4 g	width (money)	0.1070 111011
Temperatures			
Operating temperature range	-30120 °C		
Environmental Product Comp	liance		
RoHS Compliance Status	Compliant without exemptio	n	
REACH SVHC	No SVHC above 0.1 wt%		
General data			
Matarial salarm assauding to resistance	0	Number	594
Material colour according to resistance code	9	Number per sheet	594
Type of printing	neutral	Width	4 mm
UL 94 flammability rating	НВ	Operating temperature range, max.	120 °C
Operating temperature range, min.	-30 °C	Colour	white
Halogen	Yes	Basic material	Polyester, PVC-free
Printed characters	without	Recommended industries	Process, Machinery
Operating temperature range	-30120 °C		
Conductor and cable markers			
l lala man	Vaa	Canduatas O.D. mass	217
Halogen Conductor O.D., min.	Yes 10 mm	Conductor O.D., max.	317 mm
Conductor O.D., min. Text field height	4.62 mm	Text field width Conductor O.D.	21 mm 10 - 317 mm
	4.02 111111	Conductor O.D.	10-317 111111
Classifications			
ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
FCL ACC 0.1	27.40.04.01	FOLACC 10.0	07.40.04.04

ECLASS 9.1

ECLASS 11.0

ECLASS 13.0

ECLASS 15.0

Catalogue status / Drawings

ECLASS 10.0

ECLASS 12.0

ECLASS 14.0

27-40-04-01

27-28-11-02

27-28-11-02

27-28-11-02

Data sheet

CLI F 1-20 WS/GE



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

