SLA BB11R OR



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Minor component, major effect:

Clip-on attachment elements increase the mechanical resilience of the whole plug connection by

- securing the male connectors to the circuit board
- providing a vibration-proof connection between the sockets and the male connectors

Clip-on or pre-assembled - always the right solution:

- · Hard-wearing, precise fitting dovetail joint
- · Hard-wearing metal threaded inserts
- Suitable for all outlet directions

Maximum stability, minimum effort:

- Extremely resilient for frequent fastening operations
- Complete set for easy selection

The result: soldering points, contacts and overall module are more resilient against mechanical stress such as vibrations and tensile loads.

General ordering data

Version	PCB plug-in connector, Accessories, Mounting	
	block, orange, Number of poles: 0	
Order No.	<u>1604120000</u>	
Туре	SLA BB11R OR	
GTIN (EAN)	4008190182977	
Qty.	20 items	
Product data		
Packaging	Box	

Catalogue status / Drawings



SLA BB11R OR



Weidmüller Interface GmbH & Co. KG

27-46-04-05

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals				
ROHS	Conform			
Dimensions and weights				
Ţ				
Depth	12.4 mm	Depth (inches)	0.4882 inch	
Height	8.3 mm	Height (inches)	0.3268 inch	
Nidth	5.08 mm	Width (inches)	0.2 inch	
Net weight	1.17 g			
Environmental Product Comp	oliance			
		_		
RoHS Compliance Status	Compliant with exemption			
RoHS Exemption (if applicable/known)				
REACH SVHC	Lead 7439-92-1			
SCIP	00c92aa4-198d-4f32-82d1-4ccab9233b4d			
Material data				
	DDT 0.5			
nsulating material	PBT GF	Colour	orange	
Colour chart (similar)	RAL 2000	Moisture Level (MSL)		
JL 94 flammability rating	V-0	Contact material	Cu-alloy	
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C	
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C	
Temperature range, installation, min.	-25 ℃	Temperature range, installation, max.	100 °C	
Rated data acc. to IEC				
tested acc. to standard	IEC 60664-1, IEC 61	984	1	
Packing				
		VDE	00.00	
Packaging	Box	VPE length	80.00 mm	
VPE width	45.00 mm	VPE height	23.00 mm	
mportant note				
DC comformative	Comfouncity of The same	durate and developed recognificationed and delivered	o a a sudim ar imta un oti a mol	
PC conformity	Conformity: The products are developed, manufactured and delivered according international			
	recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the production of the produc			
	can be evaluated on		Siaimo on the produ	
Votes	 Long term storage of the product with average temperature of 50 °C and maximum humidity 			
	70%, 36 months		•	
Classifications				
	FC002042	ETIM 7.0	FC002042	
ETIM 6.0	EC002943	ETIM 7.0	EC002943	
ETIM 6.0 ETIM 8.0	EC002943	ETIM 9.0	EC002943	
ETIM 6.0 ETIM 8.0 ETIM 10.0	EC002943 EC002943	ETIM 9.0 ECLASS 9.0	EC002943 27-44-04-92	
ETIM 6.0 ETIM 8.0 ETIM 10.0 ECLASS 9.1	EC002943 EC002943 27-44-04-92	ETIM 9.0 ECLASS 9.0 ECLASS 10.0	EC002943 27-44-04-92 27-44-04-92	
ETIM 6.0 ETIM 8.0 ETIM 10.0 ECLASS 9.1 ECLASS 11.0	EC002943 EC002943	ETIM 9.0 ECLASS 9.0	EC002943 27-44-04-92	

Creation date 29.11.2025 09:15:12 MEZ

ECLASS 13.0

ECLASS 15.0

Catalogue status / Drawings 2

ECLASS 14.0

27-46-04-05

27-46-04-05



SLA BB11R OR



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings

Example of use

