SL 135 BB15R OR



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Minor component, major effect:

Clip-on attachment elements increase the mechanical resilience of the whole plug connection by

- securing the male connectors to the circuit board
- providing a vibration-proof connection between the sockets and the male connectors

Clip-on or pre-assembled - always the right solution:

- · Hard-wearing, precise fitting dovetail joint
- · Hard-wearing metal threaded inserts
- Suitable for all outlet directions

Maximum stability, minimum effort:

- Extremely resilient for frequent fastening operations
- Complete set for easy selection

The result: soldering points, contacts and overall module are more resilient against mechanical stress such as vibrations and tensile loads.

General ordering data

Version	PCB plug-in connector, Accessories, Mounting		
	block, orange, Number of poles: 1		
Order No.	<u>1606450000</u>		
Туре	SL 135 BB15R OR		
GTIN (EAN)	4008190179984		
Qty.	20 items		
Product data			
Packaging	Box		

1

Catalogue status / Drawings



SL 135 BB15R OR



Weidmüller Interface GmbH & Co. KG

2

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

POLIC	0 (
ROHS	Conform			
Dimensions and weights				
Depth	13.5 mm	Depth (inches)	0.5315 inch	
Height	12.6 mm	Height (inches)	0.4961 inch	
Width	7.3 mm	Width (inches)	0.2874 inch	
Net weight	1.54 g			
Environmental Product Comp	liance			
D 110 0				
RoHS Compliance Status	Compliant without exemption			
REACH SVHC	No SVHC above 0.1 wt%			
Material data				
Inculating material	PBT	Colour	orongo	
Insulating material		Colour	orange	
Colour chart (similar)	RAL 2000 V-0	Moisture Level (MSL) Contact material	Cuallan	
UL 94 flammability rating	-40 °C		Cu-alloy 70 °C	
Storage temperature, min.	-40 C -50 °C	Storage temperature, max.	100 °C	
Operating temperature, min. Temperature range, installation, min.	-50 C -25 ℃	Operating temperature, max. Temperature range, installation, max.	100 °C	
Rated data acc. to IEC				
tested acc. to standard	IEC 60664-1, IEC 61	984		
Packing				
	Box	VPE length	90.00 mm	
Packaging				
	71.00 mm	VPE height	42.00 mm	
VPE width	71.00 mm		42.00 mm	
VPE width Important note		VPE height		
VPE width Important note	Conformity: The prod	VPE height	according international	
VPE width Important note	Conformity: The prod	VPE height lucts are developed, manufactured and delivered and norms and comply with the assured proper	according international ties in the data sheet resp.	
VPE width Important note	Conformity: The prod recognized standards fulfill decorative prop	VPE height lucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Fu	according international ties in the data sheet resp.	
Packaging VPE width Important note IPC conformity Notes	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on i • Long term storage	VPE height lucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Fu	according international ties in the data sheet resp. Irther claims on the product	
VPE width Important note IPC conformity Notes	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on I	VPE height Jucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Furequest.	according international ties in the data sheet resp. Irther claims on the product	
VPE width Important note IPC conformity Notes	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on i • Long term storage	VPE height Jucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Furequest.	according international ties in the data sheet resp. irther claims on the product	
VPE width Important note IPC conformity Notes Classifications	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on i • Long term storage 70%, 36 months	VPE height Jucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Furequest. of the product with average temperature of 50 °C	according international ties in the data sheet resp. Irther claims on the product C and maximum humidity	
VPE width Important note IPC conformity Notes Classifications ETIM 6.0	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on a Long term storage 70%, 36 months	VPE height Jucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Furequest. of the product with average temperature of 50 °C	according international ties in the data sheet resp. Irther claims on the product C and maximum humidity EC002943	
VPE width Important note IPC conformity Notes Classifications ETIM 6.0 ETIM 8.0	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on a Long term storage 70%, 36 months EC002943 EC002943	VPE height Jucts are developed, manufactured and delivered and norms and comply with the assured proper verties in accordance with IPC-A-610 "Class 2". Furequest. of the product with average temperature of 50 °C ETIM 7.0 ETIM 9.0	according international ties in the data sheet resp. in the resp. in the product and maximum humidity EC002943 EC002943	
VPE width Important note IPC conformity Notes Classifications ETIM 6.0 ETIM 8.0 ETIM 10.0	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on a Long term storage 70%, 36 months EC002943 EC002943 EC002943	VPE height lucts are developed, manufactured and delivered and norms and comply with the assured proper erties in accordance with IPC-A-610 "Class 2". Furequest. of the product with average temperature of 50 °C ETIM 7.0 ETIM 9.0 ECLASS 9.0	according international ties in the data sheet resp. In the claims on the product and maximum humidity EC002943 EC002943 27-44-04-92	
VPE width Important note IPC conformity	Conformity: The prod recognized standards fulfill decorative prop can be evaluated on a Long term storage 70%, 36 months EC002943 EC002943	VPE height Jucts are developed, manufactured and delivered and norms and comply with the assured proper verties in accordance with IPC-A-610 "Class 2". Furequest. of the product with average temperature of 50 °C ETIM 7.0 ETIM 9.0	according international ties in the data sheet resp. In the claims on the product and maximum humidity EC002943 EC002943	

Creation date 29.11.2025 01:21:50 MEZ

ECLASS 15.0

Catalogue status / Drawings

27-46-04-05