


ZQV 4/3 GE**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Accessories, Cross-connector, 32 A
Order No.	1608960000
Type	ZQV 4/3 GE
GTIN (EAN)	4008 190263232
Qty.	60 items

ZQV 4/3 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	31.6 mm	Depth (inches)	1.2441 inch
Height	16.6 mm	Height (inches)	0.6535 inch
Width	2.8 mm	Width (inches)	0.1102 inch
Net weight	2.48 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version For the terminals

Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	Yes		

Dimensions

Pitch in mm (P) 6.10 mm

General

Number of poles 3 Installation advice Direct mounting

Rating data

Rated voltage 400 V Nominal current 32 A

Important note

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used. Cross connections with >10 poles have bare cut edges ex works.

Technical data

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		