

## DEK 5/6 MC NE WS


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |  |
|------------|--|
| Version    | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, white |
| Order No.  | <a href="#">1609820000</a>   |
| Type       | DEK 5/6 MC NE WS   |
| GTIN (EAN) | 4008190203436  |
| Qty.       | 1000 items   |

## DEK 5/6 MC NE WS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 6 mm   | Width (inches)  | 0.2362 inch |
| Net weight | 0.12 g |                 |             |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2 eq. |  |

## General data

|  |   |           |  |
|--|---|-----------|--|
| Material colour according to resistance code | 9   |           |  |
| Orientation of print                         | horizontal and vertical   |           |  |
| Width  | 6 mm  |           |  |
| UL 94 flammability rating                    | V-2   |           |  |
| Operating temperature range, max.            | 100 °C  |           |  |
| Operating temperature range, min.            | -40 °C  |           |  |
| Colour                                       | white   |           |  |
| Halogen                                      | No  |           |  |
| Basic material                               | Polyamide 66  |           |  |
| Printed characters                           | neutral   |           |  |
| Number of markers per packaging unit         | Form of supply  | MultiCard |  |
| compatible printer                           | <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a> |           |  |
| Number of markers per combination            | 1 MultiCard = Terminal marker   |           |  |
| Operating temperature range                  | -40...100 °C  |           |  |
| Application/manufacturer                     | Weidmueller   |           |  |

## Connector markers

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 6.00 mm |
|-----------------|---------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000761    | ETIM 7.0    | EC000761    |
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 9.0  | 27-14-11-37 |
| ECLASS 9.1  | 27-14-11-37 | ECLASS 10.0 | 27-14-11-37 |
| ECLASS 11.0 | 27-28-11-01 | ECLASS 12.0 | 27-28-11-01 |
| ECLASS 13.0 | 27-28-11-01 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**



**Drawing**

