

## DEK 5/5 MC SDR


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |  |
|------------|--|
| Version    | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, To customer specification |
| Order No.  | <a href="#">1609810000</a>   |
| Type       | DEK 5/5 MC SDR   |
| GTIN (EAN) | 4008190456597  |
| Qty.       | 200 items  |

## DEK 5/5 MC SDR

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 5 mm   | Width (inches)  | 0.1968 inch |
| Net weight | 0.12 g |                 |             |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.002 kg CO2 eq. |  |

## General data

|                                      |   |           |  |
|--------------------------------------|---|-----------|--|
| Orientation of print                 | horizontal and vertical                                       |           |  |
| Printing method                      | MC Laser  |           |  |
| Width                                | 5 mm  |           |  |
| UL 94 flammability rating            | V-2   |           |  |
| Operating temperature range, max.    | 100 °C  |           |  |
| Operating temperature range, min.    | -40 °C  |           |  |
| Colour                               | To customer specification                                     |           |  |
| Basic material                       | Polyamide 66  |           |  |
| Colour of printing                   | black   |           |  |
| Printed characters                   | Based on customer requirements (Please send M-Print PRO file) |           |  |
| Number of markers per packaging unit | Form of supply  | MultiCard |  |
| Size of labelling field              | 5 x 5 mm  |           |  |
| Number of markers per combination    | 1 MultiCard = Terminal marker                                 |           |  |
| Operating temperature range          | -40...100 °C  |           |  |
| Application/manufacturer             | Weidmueller   |           |  |

## Connector markers

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 5.00 mm |
|-----------------|---------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**

---

---

**Drawing**

---

