



**BL 3.50/21/180 SN OR BX****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Female connectors with clamping yoke screw system for connecting conductors at 3.50 mm pitch. They provide space for labelling and can be coded.

**General ordering data**

|              |                                                                                                                                       |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, female plug, 3.50 mm, Number of poles: 21, 180°, Clamping yoke connection, Clamping range, max. : 1.5 mm², Box |
| Order No.    | <a href="#">1620330000</a>                                                                                                            |
| Type         | BL 3.50/21/180 SN OR BX                                                                                                               |
| GTIN (EAN)   | 4008190154752                                                                                                                         |
| Qty.         | 24 items                                                                                                                              |
| Product data | IEC: 320 V / 17 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 28 - AWG 14                                                               |
| Packaging    | Box                                                                                                                                   |

## BL 3.50/21/180 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 18.5 mm | Depth (inches)  | 0.7283 inch |
| Height     | 13 mm   | Height (inches) | 0.5118 inch |
| Width      | 73.5 mm | Width (inches)  | 2.8937 inch |
| Net weight | 18.71 g |                 |             |

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Product Carbon Footprint Cradle to gate 0,694 kg CO2 eq.

## System Parameters

Product family OMNIMATE Signal - series BL/SL 3.50

Type of connection Field connection

Wire connection method Clamping yoke connection

Pitch in mm (P) 3.50 mm

Pitch in inches (P) 0.138 "

Conductor outlet direction 180°

Number of poles 21

L1 in mm 70.00 mm

L1 in inches 2.756 "

Number of rows 1

Pin series quantity 1

Rated cross-section 1.5 mm<sup>2</sup>

Touch-safe protection acc. to DIN VDE 57 106 Safe from finger touch

Touch-safe protection acc. to DIN VDE 0470 IP20 plugged/ IP10 unplugged

Protection degree IP20, when fully mounted

Volume resistance ≤5 mΩ

Can be coded Yes

Stripping length 6 mm

Clamping screw M 2

Screwdriver blade 0.4 x 2.5

Screwdriver blade standard DIN 5264

Plugging cycles 25

Plugging force/pole, max. 7 N

Pulling force/pole, max. 5 N

|                   |                   |                   |      |         |
|-------------------|-------------------|-------------------|------|---------|
| Tightening torque | Torque type       | Wire connection   |      |         |
|                   | Usage information | Tightening torque | min. | 0.2 Nm  |
|                   |                   |                   | max. | 0.25 Nm |

## BL 3.50/21/180 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Material data

|                                       |          |                                       |                            |
|---------------------------------------|----------|---------------------------------------|----------------------------|
| Insulating material                   | PBT      | Colour                                | orange                     |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | IIIa                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Moisture Level (MSL)                  |                            |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-alloy                   |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -30 °C   | Temperature range, installation, max. | 100 °C                     |

## Conductors suitable for connection

|                                                                     |                      |
|---------------------------------------------------------------------|----------------------|
| Clamping range, min.                                                | 0.08 mm <sup>2</sup> |
| Clamping range, max.                                                | 1.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.                             | AWG 28               |
| Wire connection cross section AWG, max.                             | AWG 14               |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                                             | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                                          | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                      |
| w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm <sup>2</sup> max. |                      |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>  |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 1.5 mm <sup>2</sup>  |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.4 mm x 1.5 mm      |

|                                        |                                        |                              |                            |      |
|----------------------------------------|----------------------------------------|------------------------------|----------------------------|------|
| Clampable conductor                    | Cross-section for conductor connection | Type                         | fine-wired                 |      |
|                                        |                                        | nominal                      | 0.5 mm <sup>2</sup>        |      |
| wire end ferrule                       |                                        | Stripping length             | nominal                    | 8 mm |
|                                        |                                        | Recommended wire-end ferrule | <a href="#">H0.5/12 OR</a> |      |
|                                        |                                        | Stripping length             | nominal                    | 6 mm |
|                                        |                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a>     |      |
| Cross-section for conductor connection |                                        | Type                         | fine-wired                 |      |
|                                        |                                        | nominal                      | 0.75 mm <sup>2</sup>       |      |
| wire end ferrule                       |                                        | Stripping length             | nominal                    | 8 mm |
|                                        |                                        | Recommended wire-end ferrule | <a href="#">H0.75/12 W</a> |      |
|                                        |                                        | Stripping length             | nominal                    | 6 mm |
|                                        |                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a>    |      |
| Cross-section for conductor connection |                                        | Type                         | fine-wired                 |      |
|                                        |                                        | nominal                      | 1 mm <sup>2</sup>          |      |
| wire end ferrule                       |                                        | Stripping length             | nominal                    | 8 mm |
|                                        |                                        | Recommended wire-end ferrule | <a href="#">H1.0/12 GE</a> |      |
|                                        |                                        | Stripping length             | nominal                    | 6 mm |
|                                        |                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>     |      |
| Cross-section for conductor connection |                                        | Type                         | fine-wired                 |      |
|                                        |                                        | nominal                      | 0.25 mm <sup>2</sup>       |      |
| wire end ferrule                       |                                        | Stripping length             | nominal                    | 8 mm |

## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

|                |                                                                                                                                                                        |                              |                                                          |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|----------------------------------------------------------|
|                |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H0,25/10 HBL</a>                             |
|                |                                                                                                                                                                        | Stripping length             | nominal 5 mm                                             |
|                |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H0,25/5</a>                                  |
|                | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                                               |
|                |                                                                                                                                                                        | nominal                      | 0.34 mm <sup>2</sup>                                     |
|                |                                                                                                                                                                        | Stripping length             | nominal 8 mm                                             |
| Reference text | The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage. | wire end ferrule             | Recommended wire-end ferrule <a href="#">H0,34/10 TK</a> |

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 12 A                   | Rated current, min. number of poles (Tu=40°C)                         | 14.5 A            |
| Rated current, max. number of poles (Tu=40°C)                             | 10 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 320 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV            |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 100 A |

## Rated data acc. to CSA

|                                   |                                                                        |                                   |                |
|-----------------------------------|------------------------------------------------------------------------|-----------------------------------|----------------|
| Institute (CSA)                   | CSA                                                                    | Certificate No. (CSA)             | 154685-1318353 |
| Rated voltage (Use group B / CSA) | 300 V                                                                  | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 10 A                                                                   | Rated current (Use group D / CSA) | 10 A           |
| Wire cross-section, AWG, min.     | AWG 28                                                                 | Wire cross-section, AWG, max.     | AWG 14         |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |                                   |                |

## Rated data acc. to UL 1059

|                                       |                                                                        |                                       |        |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (UR)                        | UR                                                                     | Certificate No. (UR)                  | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V                                                                  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 10 A                                                                   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 28                                                                 | Wire cross-section, AWG, max.         | AWG 14 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

## Packing

|           |          |            |           |
|-----------|----------|------------|-----------|
| Packaging | Box      | VPE length | 104.00 mm |
| VPE width | 84.00 mm | VPE height | 70.00 mm  |

## Type tests

|                              |            |                                                                                  |
|------------------------------|------------|----------------------------------------------------------------------------------|
| Test: Durability of markings | Standard   | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96 |
|                              | Test       | mark of origin, type identification, approval marking SEV, approval marking CSA  |
|                              | Evaluation | available                                                                        |

## BL 3.50/21/180 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                                                           |                |                                                                                    |
|-----------------------------------------------------------|----------------|------------------------------------------------------------------------------------|
| Test: Misengagement (Non-interchangeability)              | Test           | durability                                                                         |
|                                                           | Evaluation     | passed                                                                             |
|                                                           | Standard       | DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN IEC 60512 part 7 section 5 / 05.94 |
|                                                           | Test           | 180° turned with coding elements                                                   |
| Test: Clampable cross section                             | Evaluation     | passed                                                                             |
|                                                           | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.99 |
|                                                           | Conductor type | Type of conductor and conductor cross-section solid 0.2 mm <sup>2</sup>            |
|                                                           |                | Type of conductor and conductor cross-section stranded 0.2 mm <sup>2</sup>         |
|                                                           |                | Type of conductor and conductor cross-section solid 1.5 mm <sup>2</sup>            |
|                                                           |                | Type of conductor and conductor cross-section stranded 1.5 mm <sup>2</sup>         |
|                                                           |                | Type of conductor and conductor cross-section AWG 28/1                             |
|                                                           |                | Type of conductor and conductor cross-section AWG 28/19                            |
|                                                           |                | Type of conductor and conductor cross-section AWG 16/1                             |
|                                                           |                | Type of conductor and conductor cross-section AWG 16/19                            |
|                                                           | Evaluation     | passed                                                                             |
|                                                           | Standard       | DIN EN 60999-1 section 9.4 / 12.00                                                 |
|                                                           | Requirement    | 0.2 kg                                                                             |
|                                                           | Conductor type | Type of conductor and conductor cross-section AWG 28/1                             |
|                                                           |                | Type of conductor and conductor cross-section AWG 28/19                            |
| Test for damage to and accidental loosening of conductors | Evaluation     | passed                                                                             |
|                                                           | Requirement    | 0.3 kg                                                                             |
|                                                           | Conductor type | Type of conductor and conductor cross-section 2 × AWG 24/1                         |
|                                                           |                | Type of conductor and conductor cross-section 2 × AWG 24/19 with wire end ferrule  |
|                                                           | Evaluation     | passed                                                                             |
|                                                           | Requirement    | 0.4 kg                                                                             |
|                                                           | Conductor type | Type of conductor and conductor cross-section solid 1.5 mm <sup>2</sup>            |
|                                                           |                | Type of conductor and conductor cross-section stranded 1.5 mm <sup>2</sup>         |
|                                                           |                | Type of conductor and conductor cross-section AWG 16/7                             |
|                                                           | Evaluation     | passed                                                                             |
| Pull-out test                                             | Standard       | DIN EN 60999-1 section 9.5 / 12.00                                                 |
|                                                           | Requirement    | ≥5 N                                                                               |

## Technical data

|                |                                               |                                     |
|----------------|-----------------------------------------------|-------------------------------------|
| Conductor type | Type of conductor and conductor cross-section | AWG 28/1                            |
|                | Type of conductor and conductor cross-section | AWG 28/19                           |
| Evaluation     | passed                                        |                                     |
| Requirement    | ≥10 N                                         |                                     |
| Conductor type | Type of conductor and conductor cross-section | 2 × AWG 24/1                        |
|                | Type of conductor and conductor cross-section | 2 × AWG 24/19 with wire end ferrule |
| Evaluation     | passed                                        |                                     |
| Requirement    | ≥40 N                                         |                                     |
| Conductor type | Type of conductor and conductor cross-section | H05V-U1.5                           |
|                | Type of conductor and conductor cross-section | H05V-K1.5                           |
|                | Type of conductor and conductor cross-section | AWG 16/7                            |
| Evaluation     | passed                                        |                                     |

## Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes


- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Max. outer diameter of the conductor: 2.9 mm
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

## Classifications


|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |

## Drawings


### Product image




### Dimensional drawing




### Graph




### Graph



### Graph



### Graph



## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Strain reliefs



For frequent load changes: the "trailer coupling" for plug-in connectors.

The strain relief can do more than just relieve the strain on conductors:

Simply clip onto the plug and

- bundle conductors
- guide cables
- use as a connection and disconnection aid

No damage to the connecting points, clear, tidy wiring and easy to handle.

User advantages: permanent heavy-duty connections for harsh industrial environments and convenient operation ensure improved system availability.

## General ordering data

|            |                            |                                                                      |
|------------|----------------------------|----------------------------------------------------------------------|
| Type       | BL 3.50 ZE03 BK BX         | Version                                                              |
| Order No.  | <a href="#">1627820000</a> | PCB plug-in connector, Accessories, Strain relief, black, Number of  |
| GTIN (EAN) | 4008190202552              | poles: 3                                                             |
| Qty.       | 50 ST                      |                                                                      |
| Type       | BL 3.50 ZE08 BK BX         | Version                                                              |
| Order No.  | <a href="#">1627830000</a> | PCB plug-in connector, Accessories, Strain relief, black, Number of  |
| GTIN (EAN) | 4008190202576              | poles: 8                                                             |
| Qty.       | 50 ST                      |                                                                      |
| Type       | BL 3.50 ZE03 OR BX         | Version                                                              |
| Order No.  | <a href="#">1629680000</a> | PCB plug-in connector, Accessories, Strain relief, orange, Number of |
| GTIN (EAN) | 4008190202569              | poles: 3                                                             |
| Qty.       | 50 ST                      |                                                                      |
| Type       | BL 3.50 ZE08 OR BX         | Version                                                              |
| Order No.  | <a href="#">1629690000</a> | PCB plug-in connector, Accessories, Strain relief, orange, Number of |
| GTIN (EAN) | 4008190202583              | poles: 8                                                             |
| Qty.       | 50 ST                      |                                                                      |

## Coding elements



Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase.

The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery.

Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible.

The advantage: no troubleshooting during manufacture and no operational errors by the user.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | BL SL 3.5 KO OR            | Version                                                            |
| Order No.  | <a href="#">1693430000</a> | PCB plug-in connector, Accessories, Coding element, orange, Number |
| GTIN (EAN) | 4008190867447              | of poles: 1                                                        |
| Qty.       | 100 ST                     |                                                                    |

## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | BL SL 3.5 KO SW            | Version                                                           |
| Order No.  | <a href="#">1610100000</a> | PCB plug-in connector, Accessories, Coding element, black, Number |
| GTIN (EAN) | 4008190187637              | of poles: 1                                                       |
| Qty.       | 100 ST                     |                                                                   |


## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Counterpart

## SL 3.50/90F




- Pin headers for wave soldering in 3.50 mm pitch
- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
  - Housing variant: screw flange (F)
  - Packed in a cardboard box (BX)
  - Pin header can be coded

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | SL 3.50/21/90F 3.2SN OR... | Version                                                            |
| Order No.  | <a href="#">1619810000</a> | PCB plug-in connector, male header, Flange, THT solder connection, |
| GTIN (EAN) | 4008190147570              | 3.50 mm, Number of poles: 21, 90°, Solder pin length (l): 3.2 mm,  |
| Qty.       | 20 ST                      | tinned, orange, Box                                                |

## SL 3.50/180F




- Pin headers for wave soldering in 3.50 mm pitch
- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
  - Housing variant: screw flange (F)
  - Packed in a cardboard box (BX)
  - Pin header can be coded

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | SL 3.50/21/180F 3.2SN O... | Version                                                            |
| Order No.  | <a href="#">1622220000</a> | PCB plug-in connector, male header, Flange, THT solder connection, |
| GTIN (EAN) | 4008190189075              | 3.50 mm, Number of poles: 21, 180°, Solder pin length (l): 3.2 mm, |
| Qty.       | 20 ST                      | tinned, orange, Box                                                |

## SLD 3.50/90F



Two-tier pin header for wave soldering in 3.50 mm pitch. The connector is available in open, closed and flange versions. The male connectors provide space for labelling and can be coded. Packed in a cardboard box.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | SLD 3.50/42/90F 3.2SN O... | Version                                                            |
| Order No.  | <a href="#">1634000000</a> | PCB plug-in connector, male header, Flange, THT solder connection, |
| GTIN (EAN) | 4008190258450              | 3.50 mm, Number of poles: 42, 90°, Solder pin length (l): 3.2 mm,  |
| Qty.       | 10 ST                      | tinned, orange, Box                                                |


## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Counterpart

## SL 3.50/135F




Pin headers for wave soldering in 3.50 mm pitch

- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
- Housing variant: screw flange (F)
- Packed in a cardboard box (BX)
- Pin header can be coded

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | SL 3.50/21/135F 3.2SN O... | Version                                                            |
| Order No.  | <a href="#">1643520000</a> | PCB plug-in connector, male header, Flange, THT solder connection, |
| GTIN (EAN) | 4008190282288              | 3.50 mm, Number of poles: 21, 135°, Solder pin length (l): 3.2 mm, |
| Qty.       | 18 ST                      | tinned, orange, Box                                                |

## SL-SMT 3.5/180LF Box



High-temperature-resistant male header, 3.50 mm pitch.

- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
- Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
- Optimised for the SMT process
- Pin length 3.2 mm universal for all soldering methods
- Pin length 1.5 mm optimised for reflow soldering methods
- Packed either in a box (BX) or tape-on-reel (RL)
- Male header can be coded

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/180LF 3.... | Version                                                           |
| Order No.  | <a href="#">1842730000</a> | PCB plug-in connector, male header, Solder flange, THT/THR solder |
| GTIN (EAN) | 4032248354092              | connection, 3.50 mm, Number of poles: 21, 180°, Solder pin length |
| Qty.       | 18 ST                      | (l): 3.2 mm, tinned, black, Box                                   |

## SL-SMT 3.5/180G Box



High-temperature-resistant male header, 3.50 mm pitch.

- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
- Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
- Optimised for the SMT process
- Pin length 3.2 mm universal for all soldering methods
- Pin length 1.5 mm optimised for reflow soldering methods
- Packed either in a box (BX) or tape-on-reel (RL)
- Male header can be coded

## BL 3.50/21/180 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Counterpart

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/180G 3.2... | Version                                                           |
| Order No.  | <a href="#">1842500000</a> | PCB plug-in connector, male header, closed side, THT/THR solder   |
| GTIN (EAN) | 4032248353866              | connection, 3.50 mm, Number of poles: 21, 180°, Solder pin length |
| Qty.       | 20 ST                      | (I): 3.2 mm, tinned, black, Box                                   |

## SL-SMT 3.5/90LF Box



High-temperature-resistant male header, 3.50 mm pitch.

- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
- Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
- Optimised for the SMT process
- Pin length 3.2 mm universal for all soldering methods
- Pin length 1.5 mm optimised for reflow soldering methods
- Packed either in a box (BX) or tape-on-reel (RL)
- Male header can be coded

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/90LF 3.2... | Version                                                               |
| Order No.  | <a href="#">1842040000</a> | PCB plug-in connector, male header, Solder flange, THT/THR solder     |
| GTIN (EAN) | 4032248353392              | connection, 3.50 mm, Number of poles: 21, 90°, Solder pin length (I): |
| Qty.       | 18 ST                      | 3.2 mm, tinned, black, Box                                            |

## SL-SMT 3.5/180F Box



High-temperature-resistant male header, 3.50 mm pitch.

- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
- Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
- Optimised for the SMT process
- Pin length 3.2 mm universal for all soldering methods
- Pin length 1.5 mm optimised for reflow soldering methods
- Packed either in a box (BX) or tape-on-reel (RL)
- Male header can be coded

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/180F 3.2... | Version                                                           |
| Order No.  | <a href="#">1842960000</a> | PCB plug-in connector, male header, Flange, THT/THR solder        |
| GTIN (EAN) | 4032248354429              | connection, 3.50 mm, Number of poles: 21, 180°, Solder pin length |
| Qty.       | 18 ST                      | (I): 3.2 mm, tinned, black, Box                                   |

## BL 3.50/21/180 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Counterpart

## SL-SMT 3.5/90F Box




High-temperature-resistant male header, 3.50 mm pitch.

- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
- Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
- Optimised for the SMT process
- Pin length 3.2 mm universal for all soldering methods
- Pin length 1.5 mm optimised for reflow soldering methods
- Packed either in a box (BX) or tape-on-reel (RL)
- Male header can be coded

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/90F 3.2S... | Version                                                               |
| Order No.  | <a href="#">1842270000</a> | PCB plug-in connector, male header, Flange, THT/THR solder            |
| GTIN (EAN) | 4032248353620              | connection, 3.50 mm, Number of poles: 21, 90°, Solder pin length (l): |
| Qty.       | 18 ST                      | 3.2 mm, tinned, black, Box                                            |

## SL 3.50/90




Pin headers for wave soldering in 3.50 mm pitch

- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
- Housing variant: screw flange (F)
- Packed in a cardboard box (BX)
- Pin header can be coded

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SL 3.50/21/90 3.2SN OR ... | Version                                                               |
| Order No.  | <a href="#">1619030000</a> | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4008190132651              | connection, 3.50 mm, Number of poles: 21, 90°, Solder pin length (l): |
| Qty.       | 20 ST                      | 3.2 mm, tinned, orange, Box                                           |

## SL 3.50/90G



Pin headers for wave soldering in 3.50 mm pitch

- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
- Housing variant: screw flange (F)
- Packed in a cardboard box (BX)
- Pin header can be coded

## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

## Counterpart

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SL 3.50/21/90G 3.2SN OR... | Version                                                               |
| Order No.  | <a href="#">1619420000</a> | PCB plug-in connector, male header, closed side, THT solder           |
| GTIN (EAN) | 4008190139674              | connection, 3.50 mm, Number of poles: 21, 90°, Solder pin length (l): |
| Qty.       | 20 ST                      | 3.2 mm, tinned, orange, Box                                           |

## SL 3.50/180




- Pin headers for wave soldering in 3.50 mm pitch
- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
  - Housing variant: screw flange (F)
  - Packed in a cardboard box (BX)
  - Pin header can be coded

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SL 3.50/21/180 3.2SN OR... | Version                                                           |
| Order No.  | <a href="#">1621440000</a> | PCB plug-in connector, male header, open side, THT solder         |
| GTIN (EAN) | 4008190172657              | connection, 3.50 mm, Number of poles: 21, 180°, Solder pin length |
| Qty.       | 20 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |

## SL 3.50/180G



- Pin headers for wave soldering in 3.50 mm pitch
- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
  - Housing variant: screw flange (F)
  - Packed in a cardboard box (BX)
  - Pin header can be coded

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SL 3.50/21/180G 3.2SN O... | Version                                                           |
| Order No.  | <a href="#">1621830000</a> | PCB plug-in connector, male header, closed side, THT solder       |
| GTIN (EAN) | 4008190181239              | connection, 3.50 mm, Number of poles: 21, 180°, Solder pin length |
| Qty.       | 20 ST                      | (l): 3.2 mm, tinned, orange, Box                                  |


## BL 3.50/21/180 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Counterpart

## SLD 3.50/90




Two-tier pin header for wave soldering in 3.50 mm pitch. The connector is available in open, closed and flange versions. The male connectors provide space for labelling and can be coded. Packed in a cardboard box.

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SLD 3.50/42/90 3.2SN OR... | Version                                                               |
| Order No.  | <a href="#">1633540000</a> | PCB plug-in connector, male header, open side, THT solder             |
| GTIN (EAN) | 4008190257996              | connection, 3.50 mm, Number of poles: 42, 90°, Solder pin length (l): |
| Qty.       | 10 ST                      | 3.2 mm, tinned, orange, Box                                           |

## SLD 3.50/90G



Two-tier pin header for wave soldering in 3.50 mm pitch. The connector is available in open, closed and flange versions. The male connectors provide space for labelling and can be coded. Packed in a cardboard box.

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SLD 3.50/42/90G 3.2SN O... | Version                                                               |
| Order No.  | <a href="#">1633770000</a> | PCB plug-in connector, male header, closed side, THT solder           |
| GTIN (EAN) | 4008190258221              | connection, 3.50 mm, Number of poles: 42, 90°, Solder pin length (l): |
| Qty.       | 10 ST                      | 3.2 mm, tinned, orange, Box                                           |

## SL-SMT 3.5/90G Box



- High-temperature-resistant male header, 3.50 mm pitch.
- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
  - Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
  - Optimised for the SMT process
  - Pin length 3.2 mm universal for all soldering methods
  - Pin length 1.5 mm optimised for reflow soldering methods
  - Packed either in a box (BX) or tape-on-reel (RL)
  - Male header can be coded

## BL 3.50/21/180 SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany


www.weidmueller.com

## Counterpart

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/90G 1.5S... | Version                                                               |
| Order No.  | <a href="#">1761732001</a> | PCB plug-in connector, male header, closed side, THT/THR solder       |
| GTIN (EAN) | 4032248132324              | connection, 3.50 mm, Number of poles: 21, 90°, Solder pin length (l): |
| Qty.       | 20 ST                      | 1.5 mm, tinned, black, Box                                            |
| Type       | SL-SMT 3.50/21/90G 3.2S... | Version                                                               |
| Order No.  | <a href="#">1841820000</a> | PCB plug-in connector, male header, closed side, THT/THR solder       |
| GTIN (EAN) | 4032248353170              | connection, 3.50 mm, Number of poles: 21, 90°, Solder pin length (l): |
| Qty.       | 20 ST                      | 3.2 mm, tinned, black, Box                                            |

## SL-THR 3.5/135F



High-temperature-resistant male header, 3.50 mm pitch.

- Plugging direction parallel (90°), straight 180° or angled (135°) to PCB
- Housing variants: closed side (G), screw flange (F), solder flange (LF) or snap-on solder flange (RF)
- Optimised for the SMT process
- Pin length 3.2 mm universal for all soldering methods
- Pin length 1.5 mm optimised for reflow soldering methods
- Packed either in a box (BX) or tape-on-reel (RL)
- Male header can be coded

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | SL-SMT 3.50/21/135F 3.2... | Version                                                           |
| Order No.  | <a href="#">1003710000</a> | PCB plug-in connector, male header, Flange, THT/THR solder        |
| GTIN (EAN) | 4032248700332              | connection, 3.50 mm, Number of poles: 21, 135°, Solder pin length |
| Qty.       | 18 ST                      | (l): 3.2 mm, tinned, black, Box                                   |