



BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Female plugs with crimp wire connection system. The female plugs provide space for labelling and can be coded.

General ordering data

| | |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Version | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 16, 180°, Crimp connection, Clamping range, max. : 2.5 mm ² , Box |
| Order No. | 1649510000 |
| Type | BLC 5.08/16/180BR OR BX |
| GTIN (EAN) | 4008190294625 |
| Qty. | 50 items |
| Product data | IEC: 400 V / 21 A UL: 300 V / 10 A / AWG 26 - AWG 14 |
| Packaging | Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E60693 |

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 24.5 mm | Depth (inches) | 0.9646 inch |
| Height | 10.1 mm | Height (inches) | 0.3976 inch |
| Width | 83.28 mm | Width (inches) | 3.2787 inch |
| Net weight | 9.6 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

System Parameters

| | | | |
|----------------------------------------------|----------------------------------------|--------------------------------------------|------------------------------|
| Product family | OMNIMATE Signal - series BL/SL 5.08 | Type of connection | Field connection |
| Wire connection method | Crimp connection | Pitch in mm (P) | 5.08 mm |
| Pitch in inches (P) | 0.200 " | Conductor outlet direction | 180° |
| Number of poles | 16 | L1 in mm | 76.20 mm |
| L1 in inches | 3.000 " | Number of rows | 1 |
| Pin series quantity | 1 | Rated cross-section | 2.5 mm ² |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Protection degree | IP20 | Volume resistance | ≤5 mΩ |
| Can be coded | Yes | Stripping length | 5 mm |
| Plugging cycles | 25 | Plugging force/pole, max. | 8.5 N |
| Pulling force/pole, max. | 6.5 N | | |

Material data

| | | | |
|---------------------------------------|----------------------------|---------------------------------------|----------|
| Insulating material | PBT GF | Colour | orange |
| Colour chart (similar) | RAL 2000 | Insulating material group | IIIa |
| Comparative Tracking Index (CTI) | ≥ 200 | Moisture Level (MSL) | |
| UL 94 flammability rating | V-0 | Contact material | Cu-alloy |
| Layer structure of plug contact | 4...8 μm Sn hot-dip tinned | Storage temperature, min. | -40 °C |
| Storage temperature, max. | 70 °C | Operating temperature, min. | -50 °C |
| Operating temperature, max. | 100 °C | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 100 °C | | |

Conductors suitable for connection

| | | | |
|-----------------------------------------|--------------------------------------------------------------------------------|-----------------------------------------|---------------------|
| Clamping range, min. | 0.22 mm ² | Clamping range, max. | 2.5 mm ² |
| Wire connection cross section AWG, min. | AWG 24 | Wire connection cross section AWG, max. | AWG 14 |
| Flexible, min. H05(07) V-K | 0.5 mm ² | Flexible, max. H05(07) V-K | 2.5 mm ² |
| Reference text | The outside diameter of the plastic collar should not be larger than the pitch | | |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

(P), Length of ferrules is to be chosen depending on the product and the rated voltage.

Rated data acc. to IEC

| | | | |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 21 A |
| Rated current, max. number of poles (Tu=20°C) | 14.5 A | Rated current, min. number of poles (Tu=40°C) | 18 A |
| Rated current, max. number of poles (Tu=40°C) | 12.5 A | Rated voltage for surge voltage class / pollution degree II/2 | 400 V |
| Rated voltage for surge voltage class / pollution degree III/2 | 320 V | Rated voltage for surge voltage class / pollution degree III/3 | 250 V |
| Rated impulse voltage for surge voltage class/ pollution degree II/2 | 4 kV | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV | Short-time withstand current resistance | 3 x 1s with 120 A |

Rated data acc. to CSA

| | | | |
|-----------------------------------|------------------------------------------------------------------------|-----------------------------------|-----------|
| Institute (CSA) | CSA | Certificate No. (CSA) | 12400-374 |
| Rated voltage (Use group B / CSA) | 300 V | Rated voltage (Use group D / CSA) | 300 V |
| Rated current (Use group B / CSA) | 10 A | Rated current (Use group D / CSA) | 10 A |
| Wire cross-section, AWG, min. | AWG 26 | Wire cross-section, AWG, max. | AWG 14 |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. | | |

Rated data acc. to UL 1059

| | | | |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (UR) | UR | Certificate No. (UR) | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V | Rated voltage (Use group D / UL 1059) | 300 V |
| Rated current (Use group B / UL 1059) | 10 A | Rated current (Use group D / UL 1059) | 10 A |
| Wire cross-section, AWG, min. | AWG 26 | Wire cross-section, AWG, max. | AWG 14 |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. | | |

Packing

| | | | |
|-----------|-----------|------------|-----------|
| Packaging | Box | VPE length | 186.00 mm |
| VPE width | 112.00 mm | VPE height | 89.00 mm |

Type tests

| | | |
|------------------------------|------------|--------------------------------------------------------------------------------|
| Test: Durability of markings | Standard | draft DIN VDE 0627 section 6.2.2 / 09.91, DIN IEC 512 part 7 section 5 / 05.94 |
| | Test | durability |
| | Evaluation | passed |

Important note

| | |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
| Notes | <ul style="list-style-type: none"> • Additional variants on request • Rated current related to rated cross-section & min. No. of poles. • Rated cross-section depends on crimp contact used. |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002638 | ETIM 9.0 | EC002638 |
| ETIM 10.0 | EC002638 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 | | |


BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings

Product image



Dimensional drawing



Graph



BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blocks for PCB mounting



Minor component, major effect:

Clip-on attachment elements increase the mechanical resilience of the whole plug connection by

- securing the male connectors to the circuit board
- providing a vibration-proof connection between the sockets and the male connectors

Clip-on or pre-assembled - always the right solution:

- Hard-wearing, precise fitting dovetail joint
- Hard-wearing metal threaded inserts
- Suitable for all outlet directions

Maximum stability, minimum effort:

- Extremely resilient for frequent fastening operations
- Complete set for easy selection

The result: soldering points, contacts and overall module are more resilient against mechanical stress such as vibrations and tensile loads.

General ordering data

| | | |
|------------|----------------------------|--------------------------------------------------------------------|
| Type | SLA BB 12R SW | Version |
| Order No. | 1626880000 | PCB plug-in connector, Accessories, Mounting block, black, Number |
| GTIN (EAN) | 4008190198213 | of poles: 0 |
| Qty. | 100 ST | |
| Type | SLA BB 12R OR | Version |
| Order No. | 1593450000 | PCB plug-in connector, Accessories, Mounting block, orange, Number |
| GTIN (EAN) | 4008190122164 | of poles: 0 |
| Qty. | 100 ST | |
| Type | SLA BB 11R SW | Version |
| Order No. | 1692340000 | PCB plug-in connector, Accessories, Mounting block, black, Number |
| GTIN (EAN) | 4008190864965 | of poles: 0 |
| Qty. | 20 ST | |
| Type | SLA BB 11R OR | Version |
| Order No. | 1604120000 | PCB plug-in connector, Accessories, Mounting block, orange, Number |
| GTIN (EAN) | 4008190182977 | of poles: 0 |
| Qty. | 20 ST | |

Coding elements



Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery.

Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible.

The advantage: no troubleshooting during manufacture and no operational errors by the user.

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

| | | |
|------------|----------------------------|--------------------------------------------------------------------|
| Type | BLZ/SL KO BK BX | Version |
| Order No. | 1545710000 | PCB plug-in connector, Accessories, Coding element, black, Number |
| GTIN (EAN) | 4008190087142 | of poles: 1 |
| Qty. | 50 ST | |
| Type | BLZ/SL KO OR BX | Version |
| Order No. | 1573010000 | PCB plug-in connector, Accessories, Coding element, orange, Number |
| GTIN (EAN) | 4008190048396 | of poles: 1 |
| Qty. | 100 ST | |

Crimp contacts



General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | DFFC 0.22-0.35 SN 3000 | Version |
| Order No. | 1604230000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190117498 | range : 0.35 mm ² |
| Qty. | 3000 ST | |
| Type | DFFC 0.22-0.35 SN E | Version |
| Order No. | 1604250000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190042905 | range : 0.35 mm ² |
| Qty. | 250 ST | |
| Type | DFFC 0.5-1.0 SN 3000 | Version |
| Order No. | 1480000000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190179175 | range : 1 mm ² |
| Qty. | 3000 ST | |
| Type | DFFC 0.5-1.0 SN E | Version |
| Order No. | 1567060000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190166991 | range : 1 mm ² |
| Qty. | 250 ST | |
| Type | DFFC 1.5-2.5 SN 2500 | Version |
| Order No. | 1480100000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190100414 | range : 2.5 mm ² |
| Qty. | 2500 ST | |
| Type | DFFC 1.5-2.5 SN E | Version |
| Order No. | 1567070000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190059071 | range : 2.5 mm ² |
| Qty. | 250 ST | |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

... for Weidmüller DFF and ZRV contacts



Crimping tools for for turned/stamped contact

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

| | | | |
|------------|----------------------------|-----------------------------------------------------------------------------------------------|--|
| Type | HTF DFF | Version | |
| Order No. | 9014140000 | Pressing tool, Crimping tool for contacts, 0.22mm ² , 2.5mm ² , B-Crimp | |
| GTIN (EAN) | 4008190297305 | | |
| Qty. | 1 ST | | |

Auxiliary tools



More intelligent. More efficient. Quicker.
 Auxiliary tools simplify the process of connecting and configuring the connection components:

- Assembly blocks for socket connectors with IDC contacts (type BL-IDC) can be used in machines such as toggle lever presses. All conductors are connected at the same time.
- Unlocking and dismantling tools release the crimp contacts in crimped plug-in connectors (type BLC & BLAC)
- Operating levers open individual clamping points on plug-in tension clamp connectors

For better, more rapid working progress

The result: efficient, professional working progress.

General ordering data

| | | | |
|------------|----------------------------|-----------------------|--|
| Type | DFFC EW2 | Version | |
| Order No. | 1803790000 | PCB plug-in connector | |
| GTIN (EAN) | 4032248259311 | | |
| Qty. | 10 ST | | |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart

SLDF 5.08



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SLDF 5.08 L/F 16 SN OR ... | Version |
| Order No. | 1599270000 | PCB plug-in connector, male header, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4008190066826 | 180°, Flat-blade connection, Solder connection, Box |
| Qty. | 18 ST | |

SL 5.08/135



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SL 5.08/16/135 3.2SN OR... | Version |
| Order No. | 1603200000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4008190123635 | connection, 5.08 mm, Number of poles: 16, 135°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, orange, Box |

SL 5.08/135B



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SL 5.08/16/135B 3.2SN O... | Version |
| Order No. | 1605670000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190153816 | solder connection, 5.08 mm, Number of poles: 16, 135°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart

SL 5.08/180



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SL 5.08/16/180 3.2SN OR... | Version |
| Order No. | 1518660000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4008190083304 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, orange, Box |

SL 5.08/180B



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SL 5.08/16/180B 3.2SN O... | Version |
| Order No. | 1520960000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190145149 | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type | SL 5.08/16/90 3.2SN OR ... | Version |
| Order No. | 1509460000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4008190147464 | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Counterpart

www.weidmueller.com

SL 5.08/90B



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SL 5.08/16/90B 3.2SN OR... | Version |
| Order No. | 1511760000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190020552 | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/180




Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SL 5.08HC/16/180 3.2SN ... | Version |
| Order No. | 1148410000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248934867 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/16/180 3.2SN ... | Version |
| Order No. | 1146610000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248933518 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/180B



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Counterpart

www.weidmueller.com

General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SL 5.08HC/16/180B 3.2SN... | Version |
| Order No. | 1149870000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248934263 | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/16/180B 3.2SN... | Version |
| Order No. | 1147770000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248933747 | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/180G



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SL 5.08HC/16/180G 3.2SN... | Version |
| Order No. | 1149100000 | PCB plug-in connector, male header, closed side, THT solder |
| GTIN (EAN) | 4032248935017 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/16/180G 3.2SN... | Version |
| Order No. | 1147040000 | PCB plug-in connector, male header, closed side, THT solder |
| GTIN (EAN) | 4032248934065 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/90



Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type | SL 5.08HC/16/90 3.2SN B... | Version |
| Order No. | 1155200000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4050118050677 | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/16/90 3.2SN O... | Version |
| Order No. | 1147030000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4050118051360 | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Counterpart

www.weidmueller.com

SL 5.08HC/90B



Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SL 5.08HC/16/90B 3.2SN ... | Version |
| Order No. | 1155730000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4050118050219 | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/16/90B 3.2SN ... | Version |
| Order No. | 1154920000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4050118050905 | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/90G



Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type | SL 5.08HC/16/90G 3.2SN ... | Version |
| Order No. | 1155480000 | PCB plug-in connector, male header, closed side, THT solder |
| GTIN (EAN) | 4050118050448 | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/16/90G 3.2SN ... | Version |
| Order No. | 1147740000 | PCB plug-in connector, male header, closed side, THT solder |
| GTIN (EAN) | 4050118051131 | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Counterpart

www.weidmueller.com

SLDV 5.08/180



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SLD 5.08V/32/180 3.2SN ... | Version |
| Order No. | 1725790000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248062089 | connection, 5.08 mm, Number of poles: 32, 180°, Solder pin length |
| Qty. | 10 ST | (l): 3.2 mm, tinned, orange, Box |

SLDV 5.08/180B



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SLD 5.08V/32/180B 3.2SN... | Version |
| Order No. | 1726880000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248062775 | solder connection, 5.08 mm, Number of poles: 32, 180°, Solder pin |
| Qty. | 10 ST | length (l): 3.2 mm, tinned, orange, Box |

SLDV 5.08/90



Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type | SLD 5.08V/32/90 3.2 SN ... | Version |
| Order No. | 1725310000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248060719 | connection, 5.08 mm, Number of poles: 32, 90°, Solder pin length (l): |
| Qty. | 10 ST | 3.2 mm, tinned, orange, Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**SLDV 5.08/90B**

Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

General ordering data


| | | |
|------------|----------------------------|----------------------------------------------------------------------|
| Type | SLD 5.08V/32/90B 3.2 SN... | Version |
| Order No. | 1726420000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248061396 | solder connection, 5.08 mm, Number of poles: 32, 90°, Solder pin |
| Qty. | 10 ST | length (l): 3.2 mm, tinned, orange, Box |

SL-SMT 5.08/180 Box

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SL-SMT 5.08HC/16/180 3.... | Version |
| Order No. | 1838120000 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248348183 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, black, Box |

SL-SMT 5.08/180G Box

High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------|
| Type | SL-SMT 5.08HC/16/180G 3... | Version |
| Order No. | 1838350000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248348411 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 50 ST | (l): 3.2 mm, tinned, black, Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Counterpart

www.weidmueller.com

SL-SMT 5.08HC/90 Box

High-temperature-resistant, 90° angled, open male header. Packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data


| | | |
|------------|----------------------------|-------------------------------------------------------------------------------------------------------------------------------------|
| Type | SL-SMT 5.08HC/16/90 1.5... | Version |
| Order No. | 1774902001 | PCB plug-in connector, male header, open side, THT/THR solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| GTIN (EAN) | 4032248155842 | |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/16/90 3.2... | Version |
| Order No. | 1780090000 | PCB plug-in connector, male header, open side, THT/THR solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| GTIN (EAN) | 4032248165414 | |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SL-SMT 5.08HC/90G Box

High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Type | SL-SMT 5.08HC/16/90G 3.... | Version |
| Order No. | 1780320000 | PCB plug-in connector, male header, closed side, THT/THR solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| GTIN (EAN) | 4032248165643 | |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SLT 5.08B

Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Counterpart

General ordering data

| | | |
|------------|----------------------------|------------------------------------------------------------------------|
| Type | SLT 5.08/16/180B SN OR ... | Version |
| Order No. | 1611850000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4008190192730 | 180°, TOP connection, Clamping range, max. : 2.5 mm ² , Box |
| Qty. | 50 ST | |

SLS 5.08/180 SN




Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------------------|
| Type | SLS 5.08/16/180 SN OR BX | Version |
| Order No. | 1627230000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4008190199746 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm ² , |
| Qty. | 18 ST | Box |

SLS 5.08/180B



Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------------------------------------------------|
| Type | SLS 5.08/16/180B SN OR ... | Version |
| Order No. | 1627380000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4008190199890 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm ² , |
| Qty. | 18 ST | Box |

BLC 5.08/16/180BR OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Counterpart

www.weidmueller.com

SLS 5.08TB KF35



Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|------------------------------------------------------------------|
| Type | SLS 5.08/16/180TB KF SN... | Version |
| Order No. | 1846180000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4032248362462 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², |
| Qty. | 5 ST | Box |

SLS 5.08TB RF15



Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|------------------------------------------------------------------|
| Type | SLS 5.08/16/180TB RF15 ... | Version |
| Order No. | 1846100000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4032248362387 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², |
| Qty. | 5 ST | Box |