


HDC HVE 3+2 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The HVE-series high-voltage inserts are equipped with two lagging contacts.
The wire connection level is designed as a screw element.
All screw connections are equipped with a wire protection spring.

Number of poles: 5 - 12

Rated current: 24 A

Rated voltage: 830 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

General ordering data

| | |
|------------|---|
| Version | HDC insert, Male, 830 V, 20 A, Number of poles: 5, Screw connection, Installation size: 4 |
| Order No. | 1651310000 |
| Type | HDC HVE 3+2 MS |
| GTIN (EAN) | 4008190299910 |
| Qty. | 1 items |

HDC HVE 3+2 MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 64 mm | Depth (inches) | 2.5197 inch |
| Height | 35.7 mm | Height (inches) | 1.4055 inch |
| Width | 34 mm | Width (inches) | 1.3386 inch |
| Net weight | 54 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|--------------------------------------|--|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | b67daa31-7dca-434d-8290-da7fb52f83a2 |

| | | |
|---------------------|--------------------------|---------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Resistant |
| | Substance | Ammonia, watery |
| | Chemical resistance | Conditionally resistant |
| | Substance | Petrol |
| | Chemical resistance | Resistant |
| | Substance | Benzene |
| | Chemical resistance | Resistant |
| | Substance | Diesel oil |
| | Chemical resistance | Conditionally resistant |
| | Substance | Acetic acid, concentrated |
| | Chemical resistance | Resistant |
| | Substance | Potassium hydroxide |
| | Chemical resistance | Conditionally resistant |
| | Substance | Methanol |
| | Chemical resistance | Conditionally resistant |
| | Substance | Motor oil |
| | Chemical resistance | Conditionally resistant |
| | Substance | Lye, diluted |
| | Chemical resistance | Resistant |
| Substance | Hydrochlorofluorocarbons | |
| Chemical resistance | Conditionally resistant | |
| Substance | Outdoor use | |
| Chemical resistance | Conditionally resistant | |

Dimensions

| | | | |
|----------------|---------|-------------------|-------|
| Width | 34 mm | Total length base | 64 mm |
| Height of plug | 35.7 mm | | |

HDC HVE 3+2 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General data

| | | | |
|---------------------------------------|--------------|---------------------------------------|---|
| Number of poles | 5 | Tightening torque | 0.5 Nm |
| Plugging cycles, silver | ≥ 500 | Type of connection | Screw connection |
| Installation size | 4 | UL 94 flammability rating | V-0 |
| Volume resistance | ≤2 mΩ | Colour | beige |
| Insulation resistance | 1010 Ω | Insulating material | PC glass-fibre reinforced (UL-listed and railway-certified) |
| Insulating material group | IIIa | Conductor cross-section | 2.5 mm ² |
| Tightening torque, max. PE connection | 1.5 Nm | Surface finish | Silver passivated |
| Max. torque for main contact | 0.55 Nm | Type | Male |
| Pollution severity | 3 | Tightening torque, min. PE connection | 1.2 Nm |
| Basic material | Copper alloy | Min. torque for main contact | 0.5 Nm |
| Series | HVE | Rated voltage (DIN EN 61984) | 830 V |
| Rated voltage according to UL/CSA | 600 V AC/DC | Rated impulse voltage (DIN EN 61984) | 8 kV |
| Rated current (DIN EN 61984) | 20 A | Free from halogens | true |
| Low smoke acc. DIN EN 45545-2 | Yes | BG | 4 |
| Number of signal contacts | 2 | Number of power contacts | 3 |

Connection data PE

| | | | |
|---------------------------------------|-------------------|---------------------------------------|--------------|
| Connection type PE | Screw connection | Blade size, slotted (PE connection) | SD 0.8 x 4.0 |
| Stripping length PE connection | 10 mm | Tightening torque, max. PE connection | 1.5 Nm |
| Tightening torque, min. PE connection | 1.2 Nm | Fixing screw | M 4 |
| Rated cross-section | 4 mm ² | Wire cross section, AWG (PE), min. | AWG 20 |
| Wire cross section, AWG (PE), max. | AWG 12 | | |

Version

| | | | |
|---|---------------------|---|---------------------|
| Blade size, slotted (screw connection) | SD 0.6 x 3.5 | Wire connection cross section AWG, max. | AWG 14 |
| Stripping length, rated connection | 9 mm | Type of connection | Screw connection |
| Installation size | 4 | Volume resistance | ≤2 mΩ |
| Clamping screw | M 3 | Blade size | size PZ0 |
| Wire connection cross section AWG, min. | AWG 20 | Wire cross-section, solid, max. | 4 mm ² |
| Wire cross-section, solid, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross section, finely stranded, max. | 4 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Conductor cross-section, max. | 2.5 mm ² |
| Conductor cross-section, min. | 0.5 mm ² | Surface finish | Silver passivated |
| Max. torque for main contact | 0.55 Nm | Basic material | Copper alloy |
| Min. torque for main contact | 0.5 Nm | BG | 4 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000438 | ETIM 9.0 | EC000438 |
| ETIM 10.0 | EC000438 | ECLASS 14.0 | 27-44-02-05 |
| ECLASS 15.0 | 27-44-02-05 | | |

HDC HVE 3+2 MS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

