

ESG 9/17 K MC NE WS**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive
Order No.	1674760000
Type	ESG 9/17 K MC NE WS
GTIN (EAN)	4008190447649
Qty.	200 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	9 mm	Height (inches)	0.3543 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	0.43 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.003 kg CO2 eq.	

General data

Adhesive	Double-sided adhesive tape			
Material colour according to resistance code	9			
Number per sheet	40			
Version	Self-adhesive			
Width	17 mm			
UL 94 flammability rating	V-2			
Operating temperature range, max.	60 °C			
Operating temperature range, min.	-40 °C			
Colour	white			
Halogen	No			
Basic material	PA 66			
Printed characters	without			
Number of markers per packaging unit	Form of supply	MultiCard		
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2			
Number of markers per combination	1 MultiCard = Device markers			
Operating temperature range	-40...60 °C			
Application/manufacturer	Self-adhesive			

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

