

HDC 24D TSLU 1PG29G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|---|
| Version | HDC enclosures, Installation size: 4, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 29 |
| Order No. | 1655270000 |
| Type | HDC 24D TSLU 1PG29G |
| GTIN (EAN) | 4008190408275 |
| Qty. | 1 items |

HDC 24D TSLU 1PG29G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Height | 72 mm | Height (inches) | 2.8346 inch |
| Width | 43 mm | Width (inches) | 1.6929 inch |
| Net weight | 181 g | | |

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

| | | |
|---------------------|---------------------|-------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzine |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| | Substance | Water |
| | Chemical resistance | Resistant |
| | Substance | UV |
| | Chemical resistance | Unstable |
| | Substance | Ozone |
| | Chemical resistance | Unstable |

Dimensions

| | | | |
|----------------------|-----------|---------------------|-------|
| Cable entry | w. thread | Width housing C | 43 mm |
| Total length housing | 73 mm | Height of housing B | 72 mm |

HDC 24D TSLU 1PG29G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General data

| | | | |
|-----------------------------|-----------------------------|----------------|----------------|
| Housing main material | diecast aluminium | Surface finish | Powder coating |
| Protection degree | IP65, in plugged condition | EMC housings | No |
| Material of locking element | Stainless steel, rust-proof | | |

Version

| | | | |
|------------------------------|-------------------------------------|--------------------------------|-------------------------------|
| Size of cable entries | PG 29 | Top part/bottom part/lid | upper part |
| Number of cable entry on top | 0 | Number of cable entry sideways | 1 |
| Design of housing | Cable entry from side, Plug housing | Design of locking system | End-locking clamp, lower side |
| Design | high | Installation size | 4 |
| Cable entry | w. thread | Type | Plug |
| Clamp version | End-locking clamp | Internal thread | PG 29 |
| Colour (RAL) | RAL 7035 | BG | 4 |
| Suitable for ModuPlug® | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000437 | ETIM 7.0 | EC000437 |
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 9.0 | 27-44-02-02 |
| ECLASS 9.1 | 27-44-02-02 | ECLASS 10.0 | 27-44-02-02 |
| ECLASS 11.0 | 27-44-02-02 | ECLASS 12.0 | 27-44-02-02 |
| ECLASS 13.0 | 27-44-02-02 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 24D TSLU 1PG29G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

