

HDC 16B SDLU 1PG21G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: PG 21
Order No.	1658320000
Type	HDC 16B SDLU 1PG21G
GTIN (EAN)	4008190411374
Qty.	1 items

HDC 16B SDLU 1PG21G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Dimensions and weights

Height	82 mm	Height (inches)	3.2283 inch
Width	99.5 mm	Width (inches)	3.9173 inch
Mounting dimension - height	45 mm	Mounting dimension - width	105 mm
Net weight	440 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f

Chemical resistance	Substance	Acetone
	Chemical resistance	Conditionally resistant
Substance	Drilling oil	
Chemical resistance	Resistant	
Substance	Diesel	
Chemical resistance	Resistant	
Substance	Ethyl alcohol	
Chemical resistance	Resistant	
Substance	Transmission oil	
Chemical resistance	Resistant	
Substance	Hydraulic oil	
Chemical resistance	Resistant	
Substance	Coolant	
Chemical resistance	Resistant	
Substance	Petroleum benzine	
Chemical resistance	Resistant	
Substance	Sweat	
Chemical resistance	Resistant	
Substance	Premium gasoline	
Chemical resistance	Conditionally resistant	
Substance	Water	
Chemical resistance	Resistant	
Substance	UV	
Chemical resistance	Unstable	
Substance	Ozone	
Chemical resistance	Unstable	

Dimensions

Hole pitch length A2	105 mm	Cable entry	w. thread
Width housing C	43 mm	Width base C1	56.5 mm

HDC 16B SDLU 1PG21G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Total length housing	93.3 mm	Height of housing B	82 mm
Height of base B1	5 mm		

General data

Housing main material	diecast aluminium	Surface finish	Powder coating
Protection degree	IP65, in plugged condition	Protection class note	Protection class with secured cover: IP 65
EMC housings	No	Material of locking element	Stainless steel, rust-proof

Version

Size of cable entries	PG 21	Top part/bottom part/lid	lower part
Cover	with cover	Number of cable entry on top	0
Number of cable entry sideways	1	Design of cover	with cover
Design of housing	Base housing	Design of locking system	End-locking clamp, lower side
Design	Standard	Installation size	6
Cable entry	w. thread	Type	Base housing
Clamp version	End-locking clamp	Sealing	NBR
Internal thread	PG 21	Colour (RAL)	RAL 7035
BG	6	Suitable for ModuPlug®	No

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 16B SDLU 1PG21G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings