

LM MT300 15/6 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Version	LaserMark, Device markers, 6 x 15.2 mm, silver
Order No.	1686360001
Type	LM MT300 15/6 SI
GTIN (EAN)	4008 190493837
Qty.	10 items

LM MT300 15/6 SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	15.2 mm	Width (inches)	0.5984 inch
Net weight	10.03 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive		
Number per sheet	484		
Printing method	Laser print		
Version	Self-adhesive		
Width	15.2 mm		
UL 94 flammability rating	HB		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	silver		
Halogen	No		
Basic material	Polyester, PVC-free		
Printed characters	without		
Number of markers per packaging unit	4840		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
	Number of markers per combination	484	
Approval acc. to UL 969	Yes		
Number of markers per combination	1 Label sheet = 484 Device markers		
Operating temperature range	-40...150 °C		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

