

**BZT ZVL1.5/O.ZA****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

The modular ZIA distribution system for simple signal wiring is based on stackable individual modules with proven tension spring connection technology. Thanks to the integrated cross-connection and the combination of socket and pin contacts, variable distribution strips can be flexibly assembled. The base elements are simply snapped onto TS35 DIN rails and are available in various designs for 3- and 4-wire connections. This allows the system to be configured individually and tailored to the specific application.

**General ordering data**

Version	Z-series, Marker holder
Order No.	<a href="#">1676620000</a>
Type	BZT ZVL 1.5/O.ZA
GTIN (EAN)	4008190460020
Qty.	100 items

## BZT ZVL1.5/O.ZA

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	17.45 mm	Depth (inches)	0.687 inch
Height	12.9 mm	Height (inches)	0.5079 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.62 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Operating temperature	-40 °C...100 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	100 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals	End cover plate required	No
---------	-------------------	--------------------------	----

## Additional technical data

Open sides	right	Type of fixing	Plugged
Installation advice	Direct mounting	Explosion-tested version	No
Type of mounting	Snap-on		

## Dimensions

Pitch in mm (P)	5.00 mm
-----------------	---------

## General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C		

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-14-11-92
ECLASS 15.0	27-14-11-92		