

## ZQB 2.5-2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Accessories, Cross-connector, 24 A
Order No.	<a href="#">1677120000</a>
Type	ZQB 2.5-2
GTIN (EAN)	4008190467678
Qty.	50 items

## ZQB 2.5-2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	21.85 mm	Depth (inches)	0.8602 inch
Height	8.5 mm	Height (inches)	0.3346 inch
Width	1.8 mm	Width (inches)	0.0709 inch
Net weight	0.69 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	5.00 mm
-----------------	---------

### General

Number of poles	2	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

### Rating data

Rated voltage	400 V	Nominal current	24 A
---------------	-------	-----------------	------

### Important note

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used.

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03

**Technical data**

---

ECLASS 15.0

27-25-03-03

---