

**ZQV 2.5N/9 GE****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	W-Series, Cross-connector, 24 A
Order No.	<a href="#">1693870000</a>
Type	ZQV 2.5N/9 GE
GTIN (EAN)	4008190883706
Qty.	20 items
Delivery status	Discontinued
Available until	2021-12-31T00:00:00+01:00
Alternative product	<a href="#">ZQV 2.5N/9</a>

## ZQV 2.5N/9 GE

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	23 mm	Depth (inches)	0.9055 inch
Height	44.6 mm	Height (inches)	1.7559 inch
Width	2.8 mm	Width (inches)	0.1102 inch
Net weight	5.7 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60	Continuous operating temp., max.	130

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	Yes		

## Dimensions

Pitch in mm (P)	5.10 mm
-----------------	---------

## General

Number of poles	9	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Nominal current	24 A
-----------------	------

## Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used. Cross connections with >10 poles have bare cut edges ex works.
---------------------	--

## Technical data

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		