


## LM WO 36/93 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

Version	LaserMark, Conductor and cable markers, 9.5 - 22.3 mm, 36 x 93 mm, yellow
Order No.	<a href="#">1695741687</a>
Type	LM WO 36/93 GE
GTIN (EAN)	4008190924737
Qty.	10 items

## LM WO 36/93 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	36 mm	Height (inches)	1.4173 inch
Width	93 mm	Width (inches)	3.6614 inch
Net weight	8.89 g		

## Temperatures

Operating temperature range -40...150 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## General data

Adhesive	Acrylate	
Material colour according to resistance code	4	
Number per sheet	15	
Type of printing	neutral	
Version	Self-adhesive	
Width	93 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	150	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	15
Size of labelling field	36 x 25 mm	
Number of markers per combination	1 Label sheet = 15 Conductor and cable markers	
Operating temperature range	-40...150 °C	

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	25 mm <sup>2</sup>	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	9.5 mm	Text field width	35.5 mm
Text field height	25 mm	Conductor O.D.	9.5 - 22.3 mm
Cross-section for connected wire	25 - 120 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

