SLA BB11R SW



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







Similar to illustration

Minor component, major effect:

Clip-on attachment elements increase the mechanical resilience of the whole plug connection by

- securing the male connectors to the circuit board
- providing a vibration-proof connection between the sockets and the male connectors

Clip-on or pre-assembled - always the right solution:

- · Hard-wearing, precise fitting dovetail joint
- · Hard-wearing metal threaded inserts
- Suitable for all outlet directions

Maximum stability, minimum effort:

- Extremely resilient for frequent fastening operations
- Complete set for easy selection

The result: soldering points, contacts and overall module are more resilient against mechanical stress such as vibrations and tensile loads.

General ordering data

Version	PCB plug-in connector, Accessories, Mounting		
	block, black, Number of poles: 0		
Order No.	<u>1692340000</u>		
Туре	SLA BB11R SW		
GTIN (EAN)	4008190864965		
Qty.	20 items		
Product data			
Packaging	Вох		

Catalogue status / Drawings



SLA BB11R SW



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals				
ROHS	Conform			
Dimensions and weights				
Depth	12.4 mm	Depth (inches)	0.4882 inch	
Height	8.3 mm	Height (inches)	0.3268 inch	
Nidth	5.08 mm	Width (inches)	0.2 inch	
Net weight	1.14 g	width (inches)	O.Z IIICII	
Environmental Product Comp	liance			
RoHS Compliance Status	Compliant with exemptic	on.		
RoHS Compliance Status RoHS Exemption (if applicable/known)	Compliant with exemption) 6c			
	Lead 7439-92-1			
REACH SVHC SCIP	00c92aa4-198d-4f32-82d1-4ccab9233b4d			
Material data				
wateriai uata				
Insulating material	PBT GF	Colour	black	
Colour chart (similar)	RAL 9011	Moisture Level (MSL)		
JL 94 flammability rating	V-0	Contact material	Cu-alloy	
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C	
	-50 °C	Operating temperature, max.	100 °C	
Operating temperature, min.	-50 ℃ -25 °C		100 °C	
Temperature range, installation, min. Rated data acc. to IEC	-20 0	Temperature range, installation, max.	100 C	
tested acc. to standard	IEC 60664-1, IEC 61984	1		
Packing				
deking				
Packaging	Вох	VPE length	80.00 mm	
VPE width	34.00 mm	VPE height	10.00 mm	
Important note				
IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the produc			
	can be evaluated on request.			
Notes	$^{\circ}$ Long term storage of the product with average temperature of 50 $^{\circ}\text{C}$ and maximum humidity 70%, 36 months			
Classifications				
ETIM 6 O	EC002042	ETIM 7.0	EC002042	
ETIM 6.0	EC002943		EC002943	
ETIM 8.0	EC002943	ETIM 9.0	EC002943	
ETIM 10.0	EC002943	ECLASS 9.0	27-44-04-92	
		LCLACC 10.0	27 44 04 02	
	27-44-04-92	ECLASS 10.0	27-44-04-92	
ECLASS 9.1 ECLASS 11.0 ECLASS 13.0	27-44-04-92 27-46-04-05 27-46-04-05	ECLASS 10.0 ECLASS 12.0 ECLASS 14.0	27-44-04-92 27-46-04-05 27-46-04-05	

ECLASS 15.0

Catalogue status / Drawings 2

27-46-04-05



SLA BB11R SW



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings

Example of use

