


## LM WO 25/68 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

Version	LaserMark, Conductor and cable markers, 8.2 - 14.3 mm, 25 x 68 mm, yellow
Order No.	<a href="#">1695731687</a>
Type	LM WO 25/68 GE
GTIN (EAN)	4008190924713
Qty.	10 items

## LM WO 25/68 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	68 mm	Width (inches)	2.6772 inch
Net weight	10.2 g		

### Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Adhesive	Acrylate	
Material colour according to resistance code	4	
Number per sheet	28	
Type of printing	neutral	
Version	Self-adhesive	
Width	68 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	280	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	28
Size of labelling field	25 x 17 mm	
Number of markers per combination	1 Label sheet = 28 Conductor and cable markers	
Operating temperature range	-40...150 °C	

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	14.3 mm
Conductor O.D., min.	8.2 mm	Text field width	25.4 mm
Text field height	17 mm	Conductor O.D.	8.2 - 14.3 mm
Cross-section for connected wire	16 - 70 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

