


**ZDUB 2.5-2/4AN/DB GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Thanks to their compact design, Mini rail-mounted terminal blocks are ideal for working in confined spaces such as small housings and terminal boxes.

**General ordering data**

|            |                                                                                                                               |
|------------|-------------------------------------------------------------------------------------------------------------------------------|
| Version    | Z-series, Feed-through terminal, Rated cross-section: 2.5 mm <sup>2</sup> , Tension-clamp connection, yellow, Direct mounting |
| Order No.  | <a href="#">1704720000</a>                                                                                                    |
| Type       | ZDUB 2.5-2/4AN/DB GE                                                                                                          |
| GTIN (EAN) | 4008190948382                                                                                                                 |
| Qty.       | 100 items                                                                                                                     |

## ZDUB 2.5-2/4AN/DB GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                           |                            |
|---------------------------|----------------------------|
| ROHS                      | Conform                    |
| UL File Number Search     | <a href="#">UL Website</a> |
| Certificate No. (cURus)   | E60693                     |
| Certificate No. (cURusEX) | E184763                    |

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 24 mm   | Depth (inches)  | 0.9449 inch |
| Height     | 33.5 mm | Height (inches) | 1.3189 inch |
| Width      | 10.2 mm | Width (inches)  | 0.4016 inch |
| Net weight | 7.96 g  |                 |             |

## Temperatures

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C         |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Basic material            | Wemid | Colour | yellow |
| UL 94 flammability rating | V-0   |        |        |

## Rating data IECEx/ATEX

|                                |                     |                                 |                     |
|--------------------------------|---------------------|---------------------------------|---------------------|
| Certificate No. (ATEX)         | DEMKO16ATEX1808U    | Certificate No. (IECEX)         | IECEXULD16.0036U    |
| Max. voltage (ATEX)            | 550 V               | Current (ATEX)                  | 21 A                |
| Wire cross section max. (ATEX) | 2.5 mm <sup>2</sup> | Max. voltage (IECEX)            | 550 V               |
| Current (IECEX)                | 21 A                | Wire cross section max. (IECEX) | 2.5 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex eb II C Gb       | Ex 2014/34/EU label             | II 2 G D            |

## System specifications

|                                     |                                                                                                |                               |     |
|-------------------------------------|------------------------------------------------------------------------------------------------|-------------------------------|-----|
| Version                             | Tension-clamp connection, can only be bridged at the clamping point, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1                                                                                              | Number of levels              | 1   |
| Number of clamping points per level | 4                                                                                              | Number of potentials per tier | 1   |
| Levels cross-connected internally   | Yes                                                                                            | PE connection                 | No  |
| Mounting rail                       | TS 35                                                                                          | N-function                    | No  |
| PE function                         | No                                                                                             | PEN function                  | No  |

## ZDUB 2.5-2/4AN/DB GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Additional technical data

|                          |       |                     |                 |
|--------------------------|-------|---------------------|-----------------|
| Open sides               | right | Installation advice | Direct mounting |
| Explosion-tested version | Yes   | Type of mounting    | Direct mounting |

## CSA rating data

|                               |        |                       |           |
|-------------------------------|--------|-----------------------|-----------|
| Wire cross section max. (CSA) | 12 AWG | Voltage size C (CSA)  | 600 V     |
| Current size C (CSA)          | 25 A   | Certificate No. (CSA) | 12400-379 |
| Wire cross section min. (CSA) | 26 AWG |                       |           |

## Conductors for clamping (additional connection)

|                                        |                          |
|----------------------------------------|--------------------------|
| Connection type, additional connection | Tension-clamp connection |
|----------------------------------------|--------------------------|

## Conductors for clamping (rated connection)

|                                                                                         |                          |                                                                                         |                      |
|-----------------------------------------------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------|----------------------|
| Gauge to IEC 60947-1                                                                    | A2                       | Wire connection cross section AWG, max.                                                 | AWG 12               |
| Connection direction                                                                    | top                      | Stripping length                                                                        | 10 mm                |
| Type of connection                                                                      | Tension-clamp connection | Number of connections                                                                   | 4                    |
| Clamping range, max.                                                                    | 4 mm <sup>2</sup>        | Clamping range, min.                                                                    | 0.13 mm <sup>2</sup> |
| Blade size                                                                              | 0.6 x 3.5 mm             | Wire connection cross section AWG, min.                                                 | AWG 26               |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm <sup>2</sup>      | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.13 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm <sup>2</sup>      | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.13 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, max.                                    | 2.5 mm <sup>2</sup>      | Wire connection cross section, finely stranded, min.                                    | 0.13 mm <sup>2</sup> |
| Connection cross-section, stranded, max.                                                | 4 mm <sup>2</sup>        | Connection cross-section, stranded, min.                                                | 0.13 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>        | Wire connection cross-section, solid core, min.                                         | 0.13 mm <sup>2</sup> |
| Connection cross-section, finely stranded, min.                                         | 0.13 mm <sup>2</sup>     |                                                                                         |                      |

## Dimensions

|              |       |
|--------------|-------|
| TS 15 offset | 17 mm |
|--------------|-------|

## General

|                                         |        |                     |                 |
|-----------------------------------------|--------|---------------------|-----------------|
| Wire connection cross section AWG, max. | AWG 12 | Installation advice | Direct mounting |
| Wire connection cross section AWG, min. | AWG 26 | Standards           | IEC 60947-7-1   |
| Mounting rail                           | TS 35  |                     |                 |

## Rating data

|                                              |                     |                                 |               |
|----------------------------------------------|---------------------|---------------------------------|---------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 800 V         |
| Rated DC voltage                             | 800 V               | Nominal current                 | 24 A          |
| Current at maximum wires                     | 30 A                | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 8 kV          |

**ZDUB 2.5-2/4AN/DB GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data**

|                                             |        |                    |   |
|---------------------------------------------|--------|--------------------|---|
| Power loss in accordance with IEC 60947-7-x | 0.77 W | Pollution severity | 3 |
|---------------------------------------------|--------|--------------------|---|


**UL rating data**

|                                            |        |                                            |        |
|--------------------------------------------|--------|--------------------------------------------|--------|
| Conductor size Factory wiring max. (cURus) | 12 AWG | Certificate No. (cURus)                    | E60693 |
| Conductor size Field wiring min. (cURus)   | 26 AWG | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Voltage size C (cURus)                     | 600 V  | Current size C (cURus)                     | 20 A   |
| Conductor size Field wiring max. (cURus)   | 12 AWG |                                            |        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-01 |
| ECLASS 15.0 | 27-25-01-01 |             |             |

Drawings



## ZDUB 2.5-2/4AN/DB GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |                                    |
|------------|----------------------------|------------------------------------|
| Type       | ZQB 2.5-2                  | Version                            |
| Order No.  | <a href="#">1677120000</a> | Accessories, Cross-connector, 24 A |
| GTIN (EAN) | 4008190467678              |                                    |
| Qty.       | 50 ST                      |                                    |

## End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

|            |                            |                             |
|------------|----------------------------|-----------------------------|
| Type       | ZAP ZDUB                   | Version                     |
| Order No.  | <a href="#">1704750000</a> | Z-series, End plate         |
| GTIN (EAN) | 4008190948405              |                             |
| Qty.       | 50 ST                      |                             |
| Type       | ZAP ZDUB BL                | Version                     |
| Order No.  | <a href="#">1704760000</a> | Z-series, End plate         |
| GTIN (EAN) | 4008190948412              |                             |
| Qty.       | 50 ST                      |                             |
| Type       | ZAP ZDUB OR                | Version                     |
| Order No.  | <a href="#">1704770000</a> | Z-series, End plate         |
| GTIN (EAN) | 4008190948429              |                             |
| Qty.       | 50 ST                      |                             |
| Type       | ZTW ZDUB                   | Version                     |
| Order No.  | <a href="#">1704340000</a> | Z-series, Partition plate   |
| GTIN (EAN) | 4008190948597              |                             |
| Qty.       | 50 ST                      |                             |
| Type       | ZBB ZDUB                   | Version                     |
| Order No.  | <a href="#">1704740000</a> | Accessories, Fixing bracket |
| GTIN (EAN) | 4008190948399              |                             |
| Qty.       | 50 ST                      |                             |

## ZDUB 2.5-2/4AN/DB GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

|            |                            |                            |  |
|------------|----------------------------|----------------------------|--|
| Type       | MOFU 15/35 ZDUB            | Version                    |  |
| Order No.  | <a href="#">1723660000</a> | Accessories, Mounting foot |  |
| GTIN (EAN) | 4008190975531              |                            |  |
| Qty.       | 50 ST                      |                            |  |

### Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |                            |                                                           |  |
|------------|----------------------------|-----------------------------------------------------------|--|
| Type       | DEK 5/5 MC SDR             | Version                                                   |  |
| Order No.  | <a href="#">1609810000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |  |
| GTIN (EAN) | 4008190456597              | Weidmueller, To customer specification                    |  |
| Qty.       | 200 ST                     |                                                           |  |

## ZDUB 2.5-2/4AN/DB GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



ZS markers - in proven MultiCard-format - have been developed specifically for the Z-series. They have a large printing area. The hinged mechanism even allows access to cross-connectors without dismantling. Quick installation is guaranteed by the fact that the single tags are clipped on in strips. The single tags are easy to separate.


- Hinged marker area
- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | ZS 10/5 MC NE WS           | Version                                                            |
| Order No.  | <a href="#">1610000000</a> | ZS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190263171              | Allen-Bradley, white                                               |
| Qty.       | 480 ST                     |                                                                    |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 ST                     |                            |
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 ST                     |                            |

**ZDUB 2.5-2/4AN/DB GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Slotted screwdriver**

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**General ordering data**

|            |                            |                                                                     |  |
|------------|----------------------------|---------------------------------------------------------------------|--|
| Type       | SDIS SLIM 0.6X3.5X100      | Version                                                             |  |
| Order No.  | <a href="#">2749610000</a> | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |  |
| GTIN (EAN) | 4050118896350              | thickness (A): 0.6 mm                                               |  |
| Qty.       | 1 ST                       |                                                                     |  |